


SIZE	QTY	SYM	PLTD	TOL
187	4	X	NO	+/-0.0
70	2	□	NO	+/-0.0
95	6	◇	YES	+/-0.0
32	1	⊗	YES	+/-0.0
15	47	⊗	YES	+/-0.0
30	1	⊕	YES	+/-0.0

NOTES: Unless Otherwise Specified:

1. PCBs Are To Be RoHS Compliant
2. Fab Per IPC-A-600
3. Material: Epoxy Fiberglass, NEMA Grade FR-4, 4 Layers
.062 +/- .005 Inch Thickness With
2 OZ. Copper Finished On All Outer Layers,
1 OZ. Copper On All Internal Layers.
Flammability Rating: 94 V-2 Minimum.
4. Size: Cut To Dimensions And Tolerances Shown.
5. Finish: SMOBC Using Wet Mask, Or LPI Both Sides, Color Green.
Silkscreen Component Side With White Non-conductive Ink.
Gold Immersion Both Sides (Not Required For Prototype Boards)
6. Drilling: Drill Holes Per Schedule. Plate Through
Holes With Copper, .001 Inch Thick Min. All
Hole Sizes Are Specified After Plating.
Holes Location Tolerances Are +/- .003" In Relation To Center.
7. Do Not Alter Artwork To Add Logo Or Date Code,
But You May Modify Pad Size To Meet End Finish.
8. Scoring: (Not Required For Prototype Boards)



Fabrication Drawing

APPROVALS		INIT		DATE	
DRAWN		KL			
CHECK					
DESIGN					
ENGR					
SCALE = NONE		SHT 1 of 1			

LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
LT3825EFE/LT3837EFE			
Multi-Output Flyback in 1/8 Brick Format			
SIZE	Demo Circuit 950A-A/B	REV.	A