



REVISIONS			
REV	DESCRIPTION	APPR	DATE

Demo Circuit 616A Rev 1 Component Side
LTC3425

NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4, 2 OZ. COPPER THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
4. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
5. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
7. SCORING:



SIZE	QTY	SYM	PLTD
10	136	X	PLTD
70	2	□	NPLTD
125	4	◇	PLTD
31	26	⊗	PLTD
94	8	⊗	PLTD
63	8	A	PLTD
52	8	C	PLTD
59	2	D	PLTD
41	6	E	PLTD

FABRICATION DRAWING

		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900		
		TITLE: 4MHz, Polyphase™ Synchronous Boost Converter		
DRAWN CHECK DESIGN ENGR	INIT DATE	SIZE A	DEMO DC616A	REV. 1
SCALE = NONE		DES-230588		