


Linear Tech. Corp.
Demo Circuit 626A-A Rev0




REVISIONS

REV	APPR	DATE
-----	------	------

NOTES: Unless Otherwise Specified

1. MATERIAL: 4 LAYERS, 0.062" THK. FR-4 GLASS EPOXY 2 OZ. COPPER CLAD.
2. ALL HOLE SHALL BE PLATED TRHU.
3. PLATE THRU HOLES WITH COPPER .0014 MIN. THICKNESS. ALL HOLE SIZES IN HOLE TABLE ARE AFTER PLATING.
4. SILKSCREEN: WITH WHITE EPOXY NON-CONDUCTIVE INK.
5. NO SILKSCREEN ALLOWED ON PADS LANDS.
6. SOLDER MASK: LPI, GREEN.
7. NO BLOCK SOLDERMASKING OF PADS ROWS.
8. DO NOT MAKE CHANGES ON SILKSCREEN, SUCH AS COMPANY LOGO, QC STAMPS.
9. DO NOT PLATE TOOLING(3PLCS) AND SCORING(26PLCS) HOLES.
(Reference Drawing Dwg No. DC205A)
10. SCORING:



SIZE	QTY	SYM	PLTD
125	4	+	PLTD
70	2	×	NPLTD
31	6	□	PLTD
35	10	◇	PLTD
34	8	⊗	PLTD
94	14	⊗	PLTD
10	22	A	PLTD
37	2	B	PLTD

Fabrication Drawing

APPROVALS

	INIT	DATE
DRAWN		
CHECK		
DESIGN	RmB	
ENGR	PhilipK	



LINEAR
TECHNOLOGY

1630 McCarthy Blvd.
Milpitas, CA 95035
PH: (408)432-1900

TITLE: LTC1569CS8-6
DC Accurate, Tunable, Lowpass Filter

SIZE NONE Demo Circuit 626A-A REV. 0

SCALE = NONE

DES-240009

SHT 1 of 1