


REVISION HISTORY			
ECO	REV	DESCRIPTION	APPR
-	B	PRODUCTION	LEO C
			DATE
			Apr 09, 2014



NOTES : UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, FR-370HR
TOTAL OF 2 LAYERS WITH 2 OZ. CL.
THICKNESS .062 +/- .006 TOTAL OF 2 LAYERS.
FLAMMABILITY RATING: 94 V-0 MINIMUM .
0.00 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/-3MIL INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.
GOLD IMMERSION BOTH SIDES.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK TO ADD LOGO OR DATE CODE BUT MAY MODIFY PAD SIZE TO MEET END FINISH.
8. PCB's SHOULD BE RoHS COMPLIANT.

9. SCORING: FOR PANELIZED FABRICATION ONLY



SIZE	QTY	SYM	PLATED	TOL
70	2	+	NO	+/-3Mil
63	19	X	YES	+/-3Mil
31	24	□	YES	+/-3Mil
10	36	◇	YES	+/-3Mil
35	14	⊗	YES	+/-3Mil
94	2	⊗	YES	+/-3Mil



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES:
0.1XX = ± 0.01
0.0XX = ± 0.005
INTERPRET DIM AND TOL
PER ASME Y14.5M-1994
THIRD ANGLE PROJECTION

APPROVALS

PCB DES.	RB
APP ENG.	LEO CHEN
TITLE: FABRICATION DRAWING TEMPERATURE, VOLTAGE AND CURRENT MONITOR	
SIZE	IC NO.
N/A	LTC2991QMS
SCALE = NONE	REV
	1
FILENAME: 1785B_Rev1.PCB	SHT 1 OF 1

1630 MCCARTHY BLVD
FARMERSVILLE, CA 95035
TEL: 916-351-7000
WWW.LINEAR.COM
LTC CONFIDENTIAL
FOR CUSTOMER USE ONLY

LINEAR
TECHNOLOGY