



REVISIONS			
REV	DESCRIPTION	APPR	DATE

NOTES : Unless Otherwise Specified


1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
2 OZ. COPPER FINISHED ON OUTER LAYERS.
1 OZ. COPPER FINISHED ON INNER LAYERS.
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM.
3. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
4. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
5. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.

7. SCORING:



SIZE	QTY	SYM	PLTD
35	3	+	PLTD
10	8	X	PLTD
70	2	◇	NPLTD
65	4	◇	PLTD

FAB DRAWING

APPROVALS					1630 McCarthy Blvd. Milpitas, CA 95035 Ph: (408)432-1900	
			TITLE: LT3461ES6, Boost Converter			
DRAWN	INIT	DATE				
CHECK						
DESIGN	JUNE WU	12/3/02				
ENGR	Michael S.	12/3/02				
			SIZE	A	DEMO	DC627A
			REV.		A	
SCALE = NONE			DES-230595		SHT 1 of 1	