


Linear Tech. Corp.
Demo Circuit 630 RevA




SIZE	QTY	SYM	PLTD
10	5	X	PLTD
125	4	□	PLTD
94	6	◇	PLTD
70	2	⊗	NPLTD

REVISIONS


REV	APPR	DATE
-----	------	------

NOTES: UNLESS OTHERWISE SPECIFIED,

- ARTWORK P/N DC630A REV 1.
- FAB PER IPC-A-600
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4
.062 +/- .005 INCH THICKNESS WITH 2 OZ.
COPPER FINISH ON TWO LAYERS.
FLAMABILITY RATING: 94 V-2 MINIMUM .
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
- BOARD: SELECTIVE PLATED BOARD. SOLDER
MASK OVER BARE COPPER, COLOR, GREEN LPI.
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.
SILKSCREEN COMPONENT SIDE WITH WHITE NON-
CONDUCTIVE INK.
PLATE THRU ALL HOLES WITH COPPER
MIN. PLATING THICKNESS: 1 OZ. EXCEPT
WHERE PLATING NOT REQUIRED
- DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH
WITH RESPECT TO CTR. OF DRILLED PAD.
ALL HOLES FINISHED SIZE AFTER PLATING.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- SCORING



Fabrication Drawing

APPROVALS			 LINEAR TECHNOLOGY 1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
	INIT	DATE		
DRAWN			TITLE: Piezoceramic Microactuator Driver LT3469ETS8 with Boost Regulator	
CHECK				
DESIGN	RmB			
ENGR	RZheng			
			SIZE NONE	Demo Circuit 630
SCALE = NONE			DES-230608	REV. A SHT 1 of 1