


SIZE	QTY	SYM	PLTD	TOL
125	4	+	YES	+/-0.0
70	2	X	NO	+/-0.0
94	10	□	YES	+/-0.0
63	16	◇	YES	+/-0.0
31	9	⊗	YES	+/-0.0
10	54	⊗	YES	+/-0.0
35	2	⊕	NO	+/-0.0
62.99	2	⊕	NO	+/-0.0
59.06	1	⊕	YES	+/-0.0
78.74	2	⊕	YES	+/-0.0

REVISIONS


REV	APPR	DATE
-----	------	------

NOTES: UNLESS OTHERWISE SPECIFIED,

1. ARTWORK P/N DC658A REV 2 , 4-LAYER
2. FAB PER IPC-A-600
3. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4
.062 +/- .005 INCH THICKNESS WITH 2 OZ.
COPPER FINISH ON TWO OUTER LAYERS AND
1 OZ. COPPER ON TWO INTERNAL LAYERS.
FLAMABILITY RATING: 94 V-2 MINIMUM .
4. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
5. BOARD: SELECTIVE PLATED BOARD. SOLDER
MASK OVER BARE COPPER, COLOR, GREEN LPL.
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.
SILKSCREEN COMPONENT SIDE WITH WHITE NON-
CONDUCTIVE INK.
PLATE THRU ALL HOLES WITH COPPER
MIN. PLATING THICKNESS: 1 OZ. EXCEPT
WHERE PLATING NOT REQUIRED
6. DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH
WITH RESPECT TO CTR. OF DRILLED PAD.
ALL HOLES FINISHED SIZE AFTER PLATING.
7. DROP ALL UNUSED PADS ON INNER LAYERS.
8. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
9. SCORING:



Fabrication Drawing

APPROVALS		 LINEAR TECHNOLOGY 1630 McCarthy Blvd. Milpitas, CA 95035 Ph: (408)432-1900	
DRAWN	INT		DATE
CHECK	Rmb		
DESIGN	JS/DZ		
ENGR			
TITLE: LTC3456EUF Multi-Output DC/DC Converter Powered By 2-Cell, USB or Wall Adapter			
SIZE	NONE	REV. 2	
SCALE = NONE		SHT 1 of 1	