



REVISIONS		
REV	APPR	DATE



- ART01 = LAYER 1 (COMPONENT SIDE)
- ART02 = LAYER 2 (GND)
- ART03 = LAYER 3 (GND)
- ART04 = LAYER 4 (SOLDER SIDE)


NOTES : Unless Otherwise Specified

1. MATERIAL : FR4 OR EQUIVALENT EPOXY, 2 OZ. COPPER CLAD
THICKNESS .062 +/--.006 TOTAL OF 4 LAYERS
2. FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
ELECTRODEPOSITED TIN-LEAD COMPOSITION
BEFORE REFLOW , SOLDER MASK OVER BARE COPPER (SMOBC)
3. SOLDER MASK : BOTH SIDES USING LPI OR EQUIVALENT
4. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
5. ALL DIMENSIONS ARE IN INCHES
6. SCORING:



Fabrication Drawing

SIZE	QTY	SYM	PLTD
10	4	X	PLTD
94	4	Y	PLTD
70	2	Z	NPLTD

APPROVALS				1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
		TITLE: LT3468ES5/LT3468ES5-1 Photoflash Capacitor Charger High Voltage Supply			
DRAWN	INIT	DATE	SIZE	Demo Circuit 661A-A & A-B	REV.
CHECK			NONE		
DESIGN					
ENGR					
SCALE = NONE			DESIGN #		
			SHT 1 of 1		