


REVISIONS			
REV	DATE	APPR	DATE




SIZE	QTY	SYM	PLTD	TOL
10	81	□	YES	+/-0.0
40	3	+	YES	+/-0.0
65	7	×	YES	+/-0.0
70	2	◇	NO	+/-0.0
94	6	⊗	YES	+/-0.0

- ART01 = LAYER 1 (COMPONENT SIDE)
- ART02 = LAYER 2 (GND)
- ART03 = LAYER 3 (GND)
- ART04 = LAYER 4 (SOLDER SIDE)

NOTES : Unless Otherwise Specified

1. MATERIAL : FR4 OR EQUIVALENT EPOXY, 2 OZ. COPPER CLAD
THICKNESS .062 +/--.006 TOTAL OF 4 LAYERS
2. FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
ELECTRODEPOSITED TIN-LEAD COMPOSITION
BEFORE REFLOW , SOLDER MASK OVER BARE COPPER (SMOBC)
3. SOLDER MASK : BOTH SIDES USING LPI OR EQUIVALENT
4. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
5. ALL DIMENSIONS ARE IN INCHES
6. SCORING:



Fabrication Drawing

APPROVALS				1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
		TITLE: LTC3737EUF 2-Phase Dual Step-Down DC/DC Converter		SIZE: NONE Demo Circuit 664A REV.	
SCALE = NONE		DESIGN #		SHT 1 of 1	