



LAYER STRUCTURE



NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600.
2. MATERIAL: -EPOXY FIBERGLASS, NEMA GRADE FR-4
-FINISHED THICKNESS TO BE 0.062" +/- .005"
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS
AND 1 OZ. CU ON THE INNER LAYERS.
-FLAMMABILITY RATING: 94 V-0 MINIMUM.
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00" ARE PRIMARY DATUMS.
4. DRILLING: -DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, 0.001" THICK MIN.
-ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
-HOLE LOCATION TOLERANCES ARE +/-0.003"
IN RELATION TO CENTER
-FOR VIAS SIZE > 0.01", VIAS HOLES NEED TO BE PLUGGED
AND COVERED WITH SOLDERMASK.
5. FINISH: -SNOBC USING LPI BOTH SIDES, COLOR GREEN.
-GOLD IMMERSION BOTH SIDES.
(LEAD FREE SOLDER CAN BE USED FOR PROTOTYPE)
-FOR SILKSCREEN: BOTH SIDES USE WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBs ARE TO BE RoHS COMPLIANT.
8. SCORING FOR PANELIZED PCB:



UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES:

0.XX" = +/-0.01"

0.XXX" = +/-0.005"

INTERPRET DIM AND TOL

PER ASME Y14.5M-1994

THIRD ANGLE PROJECTION



1530 MCCARTHY BLVD
MILPITAS, CA 95035
PH: (408)432-1900
WWW.LINEAROT.COM
LTC CONFIDENTIAL -
FOR CUSTOMER USE ONLY



TITLE: FABRICATION DRAWING

60V LED DRIVER
WITH INTERNAL 4A SWITCH

SIZE IC NO. REV
N/A LT3952AEFE 5
DC2013A

FILENAME: DC2013A-5.PCB SHT 1 OF 1

ADDITIONAL REQUIREMENT FOR PROTOTYPE FAB ONLY:

1. OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).
1. PROVIDE COMPLIANCE CERTIFICATES FOR PRODUCTION FAB ONLY:
 1. PROVIDE COMPLIANCE CERTIFICATES FOR RoHS, REACH AND CONFLICT-FREE MINERALS.
 2. SOLDERABILITY BOARD WITH TEST RESULTS.
 3. OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).
 4. VACUUM PACKED WITH DESICCANT.
 5. FULL PANEL WITH NO REJECT.

| SIZE | QTY | SYM | PLATED | TOL |
|-------|-----|-----|--------|----------|
| 0.006 | 52 | □ | YES | +/-0.003 |
| 0.01 | 269 | ⊠ | YES | +/-0.003 |
| 0.035 | 6 | ⊠ | YES | +/-0.003 |
| 0.065 | 11 | + | YES | +/-0.003 |
| 0.095 | 8 | ◇ | YES | +/-0.003 |
| 0.07 | 2 | × | NO | +/-0.003 |