




REVISIONS		
REV	DESCRIPTION	DATE




NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4  
FINISHED THICKNESS TO BE .062 +/- .005 INCH  
WITH 2 OZ. COPPER ON TWO OUTER LAYERS AND  
1 OZ. COPPER ON TWO INTERNAL LAYERS.  
FLAMABILITY RATING: 94 V-0 MINIMUM.
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.  
0.00 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH  
HOLES WITH COPPER, .001 INCH THICK MIN. ALL  
HOLE SIZES ARE SPECIFIED AFTER PLATING.  
HOLE LOCATION TOLERANCES ARE +/- .003  
INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.  
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.
6. CONTROLLED 50 OHM IMPEDANCE (AT 2.5 GHz FREQ.) FOR LAYER 1-2.
7. SUBJECT TO CHANGE BY MANUFACTURER, DEPENDING ON DIELECTRIC  
CONSTANT DEVIATIONS. PLEASE CONSULT LTC.
8. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.

SIZE	QTY	SYM	PLTD
95	8	+	PLTD
120	2	X	PLTD
10	267	□	PLTD
65	4	◇	PLTD
70	2	⊗	NPLTD



FAB DRAWING

<b>APPROVALS</b>		 <b>LINEAR TECHNOLOGY</b>		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE			
CHECK					
DESIGN	JUNE WU	7/17/03	TITLE: LT5546EUF, IF RECEIVER, WIDE BB		
ENGR					
			SIZE	DEMOS	REV.
			A	DC696A	A
SCALE = NONE			DES-260		SHT 1 of 1