



REVISIONS			
REV	DESCRIPTION	APPR	DATE



NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
2 OZ. COPPER FINISHED ON OUTER LAYERS.
THICKNESS .062 +/- .006 TOTAL OF 2 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: DIMENSIONS AND TOLERANCES SHOWN.
0.000 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, .001 INCH THICK MIN. ALL
HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003
INCH IN RELATION TO CENTER
5. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. SCORING:



FAB DRAWING

SIZE	QTY	SYM	PLTD
65	13	+	PLTD
35	23	X	PLTD
10	56	□	PLTD
70	2	◇	NPLTD

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON ANGLE ±1 2 PLACE ±.01 3 PLACE ±.005 INTERPRET DIM AND TOL PER ASME Y14.5M - 1994	APPROVALS			
	DRAWN	INIT	DATE	
	CHECK			
	DESIGN	J. Wu	6/23/04	
	ENGR	M. Thoren	6/23/04	
TITLE:				LTC1867CGN, 16-Bit, 8-Channel 200ksps ADC
SIZE				A
DEMO				DC806A
REV.				A
SCALE = NONE				DES- 250076
				SHT 1 of 1

