

REVISIONS		
REV	APPR	DATE

NOTES: UNLESS OTHERWISE SPECIFIED:

- ARTWORK P/N Demo Circuit 814B Rev1
- FAB PER IPC-A-600, 2-LAYERS
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4 .062 +/- .005 INCH THICKNESS WITH 2 OZ. COPPER FINISH ON TWO OUTER LAYERS. FLAMABILITY RATING: 94 V-2 MINIMUM .

- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.

- BOARD: SELECTIVE PLATED BOARD. SOLDER MASK OVER BARE COPPER, SOLDER, GREEN LPI, WHITE TIN IMMERSION (OMIKRON) BOTH SIDES. SILKSCREEN COMPONENT SIDE WITH WHITE NON-CONDUCTIVE INK.



- PLATE THRU ALL HOLES WITH COPPER MIN. PLATING THICKNESS: 1 OZ. EXCEPT WHERE PLATING NOT REQUIRED

- DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH WITH RESPECT TO CTR. OF DRILLED PAD. ALL HOLES FINISHED SIZE AFTER PLATING.

- DROP ALL UNUSED PADS ON INNER LAYERS.

- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.

- SCORING:



SIZE	QTY	SYM	PLTD	TOL
8	7	+	YES	+/-3mils
25	6	X	YES	+/-3mils
35	4	□	YES	+/-3mils

Fabrication Drawing

APPROVALS		TITLE:	
DRAWN	INIT	DATE	
CHECK			
DESIGN	Rmb		
ENGR	Ernie6		
		SIZE	REV. 1
		NONE	
		Demo Circuit 814B	
SCALE = NONE		DES-24xxxx	SHT 1 of 1



LINEAR

TECHNOLOGY

1630 McCarthy Blvd.

Milpitas, CA 95035

Ph: (408)432-1900