

REVISIONS		
REV	APPR	DATE


- ART01 = LAYER 1 (COMPONENT SIDE)
- ART02 = LAYER 2 (GND)
- ART03 = LAYER 3 (GND)
- ART04 = LAYER 4 (SOLDER SIDE)

SCORED : FOR PRODUCTION FABRICATION ONLY
NOT REQUIRED FOR PROTOTYPE BOARD

1.950"


NOTES : Unless Otherwise Specified

- MATERIAL : FR4 OR EQUIVALENT EPOXY, 2 OZ. COPPER CLAD
THICKNESS .062 +/--.006 TOTAL OF 4 LAYERS
- FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
ELECTRODEPOSITED TIN-LEAD COMPOSITION
BEFORE REFLOW , SOLDER MASK OVER BARE COPPER (SMOBC)
- SOLDER MASK : BOTH SIDES USING LPI OR EQUIVALENT
- SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
- ALL DIMENSIONS ARE IN INCHES
- SCORING:



Fabrication Drawing

APPROVALS				1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE			
CHECK					
DESIGN					
ENGR					
			TITLE: LT6522CDD/LT6522CS8 Video Line Driver & Receiver		
			SIZE NONE	Demo Circuit 815A	REV.
SCALE = NONE			DESIGN #		SHT 1 of 1



SIZE	QTY	SYM	PLTD	TOL
70	2	+	NO	+/-0.0
94	6	X	YES	+/-0.0
40	9	□	YES	+/-0.0
55	20	◇	YES	+/-0.0
10	29	⊗	YES	+/-0.0
62	4	⊗	YES	+/-0.0
126	4	⊕	NO	+/-0.0
35	16	⊖	YES	+/-0.0