



NOTES : UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600.
LEAD FREE ASSEMBLY COMPLIANT ISOLA
FR-370HR OR EQUIVALENT.
2. MATERIAL:
1 OZ. COPPER FINISH ON EXTERNAL LAYERS.
1 OZ. COPPER FINISH ON INTERNAL LAYERS.
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
FLAMMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: DIMENSIONS SHOWN AND TOLERANCES +/-0.010.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER .001 INCH THICK MIN. ALL
HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/-3mil
INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPT BOTH SIDES COLOR GREEN.
GOLD IMMERSION BOTH SIDES.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
7. DO NOT ALTER ARTWORK TO ADD LOGO OR DATE CODE BUT MAY
MODIFY PAD SIZE TO MEET END FINISH.
8. PCB's SHOULD BE RoHS COMPLIANT.

9. SCORING: FOR PANELIZED FABRICATION ONLY



LAYER STRUCTURE



SIZE	QTY	SYM	PLATED	TOL
70	2	+	NO	±3mil
94	5	X	YES	±3mil
35	16	□	YES	±3mil
31	4	◇	YES	±3mil
10	16	⊗	YES	±3mil

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES:
0.XX ± 0.01
0.XXX ± 0.005
INTERPRET DIM AND TOL
PER ASME Y14.5M-1994
THIRD ANGLE PROJECTION

APPROVALS

PCB DES.
APP. ENG.

LINEAR TECHNOLOGY

1630 MCQUARTY BLVD
MILPITAS, CA 95035
PH: (408)432-1900
FAX: (408)432-1901
LTC CONFIDENTIAL
FOR CUSTOMER USE ONLY

TITLE: FABRICATION DRAWING
45V VIN, MICROPPOWER, LOW NOISE
200mA LDO WITH OUTPUT DISCHARGE

SIZE IC NO. LT3061EDCB/LT3062EDCB
N/A DC2177A

REV 2

SCALE = NONE

FILENAME: 2177A-Rev2.PCB

SHT 1 OF 1