


REVISIONS			
REV	DESCRIPTION	APPR	DATE
A	PROTOTYPE RELEASE		




LINEAR TECHNOLOGY
DC824A * LTC3208EUH
Multidisplay LED Controller
DATE: 12-17-04

SHOWN FROM COMPONENT SIDE

SIZE	QTY	SYM	PLTD
35	39	+	PLTD
12	100	V	PLTD
190	4	W	PLTD
64	2	X	PLTD
72	2	Y	NPLTD
10	9	Z	PLTD


NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4
FINISHED THICKNESS TO BE 0.062" +/- .005"
WITH 2 OZ. COPPER ON THE OUTER LAYERS AND
2 OZ. COPPER ON THE INTERNAL LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, 0.001" THICK MIN.
ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- 0.003"
IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES, COLOR GREEN.
WHITE TIN IMMERSION (OMIKRON).
FOR SILKSCREEN: USE WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
7. SCORING FOR PANELIZED PCB:



8. PLEASE LOOK AT THE README FILE FOR THE OTHER REQUIREMENTS.

Fabrication Drawing

APPROVALS			 1630 MCCATHY BLVD MILPITAS, CA 95035 PH: (408)432-1900 LTC CONFIDENTIAL- FOR CUSTOMER USE ONLY	
	INIT	DATE		
DRAWN			TITLE: FABRICATION DRAWING Multidisplay LED Controller	
CHECK				
DESIGN	NICK C.	12-17-04		
ENGR	TED H.	09-01-04		
			SIZE	REV.
			A	A
			DC824A * LTC3208EUH	
SCALE = NONE			DES- 0000	SHT 1 of 1