

REVISIONS			
REV		APPR	DATE

**NOTES: UNLESS OTHERWISE SPECIFIED.**

- ARTWORK P/N Demo Circuit 826B Rev 0.
- FAB PER IPC-A-600, 2 LAYERS
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4  
.062 +/- .005 INCH THICKNESS WITH 2 OZ.  
COPPER FINISH ON TWO OUTER LAYERS.  
FLAMABILITY RATING: 94 V-2 MINIMUM .


- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.  
0.00 ARE PRIMARY DATUMS.

- BOARD: SELECTIVE PLATED BOARD. SOLDER MASK OVER BARE COPPER, COLOR, GREEN LPI, WHITE TIN IMMERSION (OMIKRON) BOTH SIDES, SILKSCREEN COMPONENT SIDE WITH WHITE NON-CONDUCTIVE INK.


PLATE THRU ALL HOLES WITH COPPER  
MIN. PLATING THICKNESS: 1 OZ. EXCEPT  
WHERE PLATING NOT REQUIRED

- DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH  
WITH RESPECT TO CTR. OF DRILLED PAD.  
ALL HOLES FINISHED SIZE AFTER PLATING.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.


- SCORING:



# Fabrication Drawing

APPROVALS		<div>  <div> <b>LINEAR</b> TECHNOLOGY           <div> 1630 McCarthy Blvd. Milpitas, CA 95035 Ph: (408)432-1900 </div> </div> </div>	
DRAWN	NIT		
CHECK	DATE		
DESIGN	RevB		
ENGR	Dillen R		
TITLE:		On/Off Controller	
SIZE	NONE	Demo Circuit 826B	REV. 0
SCALE - NONE		DES-26xxx	SHT 1 of 1

Linear Tech. Corp.  
Demo Circuit 826B Rev0  
Component Side



SIZE	QTY	SYM	PLATED	TOL
63	7	+	YES	+/-3M/i
70	2	X	NO	+/-3M/i
31	9	□	YES	+/-3M/i
8	12	◇	YES	+/-3M/i