


REVISIONS			
REV	DESCRIPTION	APPR	DATE
A	PROTOTYPE RELEASE		




SHOWN FROM COMPONENT SIDE


SIZE	QTY	SYM	PLTD	TOL
0.07	2	+	NO	+/-0.003"
0.094	4	X	YES	+/-0.003"
0.012	29	□	YES	+/-0.003"

NOTES: UNLESS OTHERWISE SPECIFIED

- FAB PER IPC-A-600
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4
FINISHED THICKNESS TO BE 0.062" +/- .005"
FLAMABILITY RATING: 94 V-0 MINIMUM .
TOTAL OF 2 LAYERS.
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00" ARE PRIMARY DATUMS.
- DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.001" THICK MIN.
ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/-0.003" IN RELATION TO CENTER
- FINISH: WHITE TIN IMMERSION (OMIKRON).
SMOBC USING LPI BOTH SIDES, COLOR GREEN.
SILKSCREEN: USING WHITE NON-CONDUCTIVE EPOXY INK.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- SCORING FOR PANELIZED PCB:



- PLEASE LOOK AT THE README FILE FOR THE OTHER REQUIREMENTS.

APPROVALS			 LINEAR TECHNOLOGY 1630 MCCATHY BLVD MILPITAS, CA 95035 PH: (408)432-1900 LTC CONFIDENTIAL- FOR CUSTOMER USE ONLY	
	INIT	DATE		
DRAWN			TITLE: FABRICATION DRAWING NEGATIVE VOLTAGE DIODE-OR CONTROLLER AND MONITOR	
CHECK				
DESIGN	KIM T.	11-03-04		
ENGR	MITCHELL L.	11-03-04		
			SIZE A	REV. A
			DC852A * LTC4354CDDDB	
SCALE = NONE			DES- 0000	SHT 1 of 1