



REVISIONS		
REV	DESCRIPTION	DATE




NOTES : Unless Otherwise Specified

1. MATERIAL : FR4 OR EQUIVALENT EPOXY, 2 OZ. COPPER CLAD
THICKNESS .062 +/--.006 TOTAL OF 4 LAYERS
2. FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.
BEFORE REFLOW , SOLDER MASK OVER BARE COPPER (SMOBC)
3. SOLDER MASK : BOTH SIDES USING GREEN LPI
4. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
5. ALL DIMENSIONS ARE IN INCHES
6. SCORING:



SIZE	QTY	SYM	PLTD	TOL
72	2	+	NO	+/-0.0
95	4	X	YES	+/-0.0
15	6	□	YES	+/-0.0
40	3	◇	YES	+/-0.0

Fabrication Drawing

<div>APPROVALS</div> <table><tr><td></td><td>INIT</td><td>DATE</td></tr><tr><td>DRAWN</td><td></td><td></td></tr><tr><td>CHECK</td><td></td><td></td></tr><tr><td>DESIGN</td><td></td><td></td></tr><tr><td>ENGR</td><td></td><td></td></tr></table>				INIT	DATE	DRAWN			CHECK			DESIGN			ENGR			<div> LINEAR TECHNOLOGY</div> <div>1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900</div>		
	INIT	DATE																		
DRAWN																				
CHECK																				
DESIGN																				
ENGR																				
			500mA, 1.25MHz Synchronous Boost Converter																	
SIZE		A	DEMO BRD	DC856A	REV. LTC3427EDC															
			SHT 1 of 1																	
SCALE = NONE																				