

| SIZE  | QTY | SYM            | PLATED | TOL      |
|-------|-----|----------------|--------|----------|
| 0.006 | 25  | + <sup>A</sup> | YES    | +/-0.003 |
| 0.01  | 73  | + <sup>B</sup> | YES    | +/-0.003 |
| 0.035 | 3   | + <sup>C</sup> | YES    | +/-0.003 |
| 0.055 | 10  | + <sup>E</sup> | YES    | +/-0.003 |
| 0.095 | 10  | + <sup>H</sup> | YES    | +/-0.003 |
| 0.07  | 2   | X              | NO     | +/-0.003 |
| 0.187 | 4   | +              | NO     | +/-0.003 |


**ADDITIONAL REQUIREMENT FOR PROTOTYPE FAB ONLY:**

1. OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).

**ADDITIONAL REQUIREMENTS FOR PRODUCTION FAB ONLY:**


1. PROVIDE COMPLIANCE CERTIFICATES FOR RoHS, REACH AND CONFLICT-FREE MINERALS.
2. SOLDERABILITY BOARD WITH TEST RESULTS.
3. OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).
4. VACUUM PACKED WITH DESICCANT.
5. FULL PANEL WITH NO REJECT.


## LAYER STRUCTURE



## NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600.
2. MATERIAL: -EPOXY FIBERGLASS, NEMA GRADE FR-4  
-FINISHED THICKNESS TO BE 0.062" +/- .005"  
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS  
AND 1 OZ. CU ON THE INNER LAYERS.  
-FLAMMABILITY RATING: 94 V-0 MINIMUM.
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.  
0.00" ARE PRIMARY DATUMS.
4. DRILLING: -DRILL HOLES PER SCHEDULE. PLATE THROUGH  
HOLES WITH COPPER, 0.001" THICK MIN.  
-ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.  
-HOLE LOCATION TOLERANCES ARE +/-0.003"  
IN RELATION TO CENTER
5. FINISH: -SMOBC USING LPI BOTH SIDES, COLOR GREEN.  
-GOLD IMMERSION BOTH SIDES.  
(LEAD FREE SOLDER CAN BE USED FOR PROTOTYPE)  
-FOR SILKSCREEN: BOTH SIDES USE WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.  
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBS ARE TO BE RoHS COMPLIANT.
8. SCORING FOR PANELIZED PCB:



|  |              |   |     |
|--|--------------|---|-----|
| UNLESS OTHERWISE SPECIFIED   |              |  <b>LINEAR TECHNOLOGY</b><br>1630 MCCARTHY BLVD<br>MILPITAS, CA 95035<br>PH: (408)432-1900<br>www.linear.com<br>LTC CONFIDENTIAL-<br>FOR CUSTOMER USE ONLY |     |
| DIMENSIONS ARE IN INCHES<br>TOLERANCES:<br>0.XX" = ±0.01"<br>0.XXX" = ±0.005"<br>INTERPRET DIM AND TOL<br>PER ASME Y14.5M-1994<br>THIRD ANGLE PROJECTION |              | TITLE: FABRICATION DRAWING<br><br><b>DUAL-CHANNEL LOW NOISE BIAS GENERATORS</b>   |     |
| SIZE   | IC NO.       | LT3095EUDD  | REV |
| N/A  | DEMO CIRCUIT | 2270A   | 3   |
| FILENAME: DC2270A-3.PCB  |              | SHT 1 OF 1  |     |