



LAYER 1 (COMPONENT SIDE)
 LAYER 2 (GND)
 LAYER 3 (GND)
 LAYER 4 (SOLDER SIDE)
 4 LAYERS
 .062"


NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
2 OZ. COPPER FINISHED ON OUTER LAYERS.
1 OZ. COPPER FINISHED ON INNER LAYERS.
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, .001 INCH THICK MIN. ALL
HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003
INCH IN RELATION TO CENTER
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.
OR LEAD FREE SOLDER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. SCORING:



FAB DRAWING

APPROVALS						 1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	CHECK	INIT	DATE				TITLE: LT3506AEDHDP/LT3506EDHD
							1.1MHz/575KHz
DESIGN		A Karpova	4/26/06	DUAL MONOLITHIC 1.6A STEP-DOWN REGULATOR			
ENGR		WalkerBai	4/26/06				
				SIZE A		DEMO	REV. A
						DC958A	
SCALE = NONE						SHT 1 of 1	



LINEAR TECHNOLOGY CORPORATION
DC958A
05/02/06