


REVISIONS		
REV	DESCRIPTION	DATE




LAYER STACKUP

- ART01 = LAYER 1 (COMPONENT SIDE)
- ART02 = LAYER 2 (GND)
- ART03 = LAYER 3 (GND)
- ART04 = LAYER 4 (SOLDER SIDE)

NOTES : Unless Otherwise Specified

- FAB PER IPC-A-600.
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.  
2 OZ. COPPER FINISH ON OUTER LAYERS.  
1 OZ. COPPER FINISH ON INNER LAYERS.  
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.  
FLAMABILITY RATING: 94 V-0 MINIMUM .  
3. SIZE: DIMENSIONS SHOWN AND TOLERANCES +/- .010.  
0.000 ARE PRIMARY DATUMS.
- DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.  
HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
- FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.  
SILVER IMMERSION BOTH SIDES.
- SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- SCORING:



Fabrication Drawing

SIZE	QTY	SYM	PLTD	TOL
0.07	2	+	NO	+/-0.003
0.187	4	X	YES	+/-0.003
0.02	10	□	YES	+/-0.003
0.035	9	◇	YES	+/-0.003
0.01	43	⊗	YES	+/-0.003
0.095	5	⊗	YES	+/-0.003
0.033	2	⊕	YES	+/-0.003

UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN INCHES  
TOLERANCES ON ANGLE ± 1  
2 PLACE ± .01 3 PLACE ± .005  
INTERPRET DIM AND TOL  
PER ASME Y14.5M - 1994

APPROVALS		INIT		DATE	
DRAWN	CHECK				
DESIGN	ENGR	Helen	D.CANNY	11/22/05	11/22/05

TITLE:		LTC3824EMSE	
High Voltage, P-CH MOSFET Step-Down Controller		REV. A	
SIZE	A	DC960A	REV. A

SCALE = NONE		DES-250	
		SHEET 1 of 1	

1630 McCarthy Blvd.  
Milpitas, CA 95035  
PH: (408)432-1900

LINEAR TECHNOLOGY