

SIZE	QTY	SYM	PLATED	TOL
0.006	19	⊗	YES	+/-0.003
0.01	308	×	YES	+/-0.003
0.035	11	⊠	YES	+/-0.003
0.065	7	□	YES	+/-0.003
0.095	4	⊕ <sup>A</sup>	YES	+/-0.003
0.07	2	◇	NO	+/-0.003
0.187	4	+	NO	+/-0.003


#### ADDITIONAL REQUIREMENT FOR PROTOTYPE FAB ONLY:

1. OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).

#### ADDITIONAL REQUIREMENTS FOR PRODUCTION FAB ONLY:


1. PROVIDE COMPLIANCE CERTIFICATES FOR RoHS, REACH AND CONFLICT-FREE MINERALS.
2. SOLDERABILITY BOARD WITH TEST RESULTS.
3. OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).
4. VACUUM PACKED WITH DESICCANT.
5. FULL PANEL WITH NO REJECT

## LAYER STRUCTURE



## NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600.
2. MATERIAL: -EPOXY FIBERGLASS, NEMA GRADE FR-4  
-FINISHED THICKNESS TO BE 0.062" +/- .005"  
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS  
AND 1 OZ. CU ON THE INNER LAYERS.  
-FLAMMABILITY RATING: 94 V-0 MINIMUM.
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.  
0.00" ARE PRIMARY DATUMS.
4. DRILLING: -DRILL HOLES PER SCHEDULE. PLATE THROUGH  
HOLES WITH COPPER, 0.001" THICK MIN.  
-ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.  
-HOLE LOCATION TOLERANCES ARE +/-0.003"  
IN RELATION TO CENTER
5. FINISH: -SMOBC USING LPI BOTH SIDES, COLOR GREEN.  
-GOLD IMMERSION BOTH SIDES.  
(LEAD FREE SOLDER CAN BE USED FOR PROTOTYPE)  
-FOR SILKSCREEN: BOTH SIDES USE WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.  
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBs ARE TO BE RoHS COMPLIANT.
8. SCORING FOR PANELIZED PCB:



9. DESIGN HAS SOLDER MASK DEFINED PADS ON U1. U1 SOLDER MASK  
SIZE IS 20 MIL AND PAD SIZE IS 24 MIL. DO NOT CHANGE ANY  
SIZE ON THIS COMPONENT.

UNLESS OTHERWISE SPECIFIED		1630 MCCARTHY BLVD MILPITAS, CA 95035 PH: (408)432-1900 www.linear.com LTC CONFIDENTIAL- FOR CUSTOMER USE ONLY	
DIMENSIONS ARE IN INCHES		<b>LINEAR TECHNOLOGY</b>	
TOLERANCES:		TITLE: FABRICATION DRAWING	
0.XX" = ±0.01"		60V, 3A STEP-DOWN $\mu$ MODULE <sup>®</sup> REGULATOR	
0.XXX" = ±0.005"		SIZE IC NO. LTM8073EY	
INTERPRET DIM AND TOL PER ASME Y14.5M-1994		N/A DEMO CIRCUIT 2389A	
THIRD ANGLE PROJECTION		REV 2	
		FILENAME: DC2389A-2.PCB	
		SHT 1 OF 1	