


REVISION HISTORY			
ECO	REV	DESCRIPTION	APPROVED
-	2	2ND PROTOTYPE	KWB
			10-14-15

NOTES: UNLESS OTHERWISE SPECIFIED

1. WORKMANSHIP SHALL BE IN ACCORDANCE WITH IPC-A-610
2. MAXIMUM SOLDER TEMPERATURE IS 250 DEGREES CELSIUS
3. DEWELTIZE BOARDS AFTER ASSEMBLY AND ROUTE-OUT THE BREAKOUT TABS ON FOUR SIDES OF THE BOARD
4. PARTS TO OMIT WILL BE SPECIFIED ON THE BILL OF MATERIALS. LOCATIONS OF OMITTED PARTS SHALL BE FREE OF MATERIALS. MASK THE SOLDER STENCIL WHERE SMT PARTS ARE OMITTED.
5. ASSEMBLY PROCESS SHALL INCLUDE: REFLOW SOLDER TOP SIDE SMD
6. DO NOT APPLY ANY KIND OF ASSEMBLY STAMP OR QA STAMP TO ANY BOARD
7. INSTALL SHUNTS AS SHOWN
8. MARK ASSEMBLY TYPE WITH BLACK PERMANENT MARKER WHERE SHOWN
9. SOLDER PEM NUTS ON BACK SIDE OF BOARD (2 PLACES)



APPROVALS		LTC CONFIDENTIAL FOR CUSTOMER USE ONLY	
PCB DES.	KWB	1630 McCarthy Blvd. Milpitas, CA 95035 Phone: (408) 432-1900 Fax: (408) 434-0507 www.linear.com	
APP ENG.	KWB	TITLE: TOP ASSEMBLY DRAWING ANYSIDE ISOLATED SWITCH CONTROLLER	
		SIZE	IC NO.
		N/A	LTM91001Y
		DEMO CIRCUIT 2423A	
		REV.	2
SCALE = 1:1		DATE: Wednesday, October 14th, 2015	SHEET 1 OF 1