


SIZE	QTY	SYM	PLATED	TOL
95	4	+	YES	+/-0.003
70	2	X	NO	+/-0.003
35	3	□	YES	+/-0.003
8	12	◇	YES	+/-0.003
6	3	⊗	YES	+/-0.003

NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4
 - FINISHED THICKNESS TO BE 0.062" +/- .005"
 - TOTAL OF 2 LAYERS WITH 2 OZ. CU ON ALL LAYERS
 - FLAMMABILITY RATING: 94 V-0 MINIMUM.
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00" ARE PRIMARY DATUMS.
4. DRILLING: -DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.001" THICK MIN.
-ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
-HOLE LOCATION TOLERANCES ARE +/-0.003" IN RELATION TO CENTER
-FOR VIAS SIZE > 0.01", VIAS HOLES NEED TO BE PLUGGED AND COVERED WITH SOLDERMASK.
-GOLD IMMERSION BOTH SIDES.
5. FINISH: -SNOBC USING LPI BOTH SIDES, COLOR GREEN.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBs ARE TO BE RoHS COMPLIANT.
8. SCORING:



LINEAR TECHNOLOGY 1630 MCCARTHY BLVD MILPITAS, CA 95035 PH: (408) 352-1800 WWW.LINEAR.COM LTC CONFIDENTIAL - FOR CUSTOMER USE ONLY		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES: 0.XX" = 0.01" 0.XXX" = 0.005" INTERPRET DIM AND TOL PER ASME Y14.5M-1994 THIRD ANGLE PROJECTION	
TITLE: FABRICATION DRAWING LOW NOISE 15V BIAS GENERATOR			
SIZE	IC NO.	REV	FILENAME:
N/A	LT3048EDC-15 DC2120A	2	DC2120A-2.PCB
			SHT 1 OF 1

