



REVISIONS			
REV	DESCRIPTION	APPR	DATE

NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4, 4 OZ. COPPER ON OUTER LAYER, 2 OZ. COPPER ON INNER LAYER, THICKNESS .062 +/- .006 TOTAL OF 6 LAYERS. FLAMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING. HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
5. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. SCORING:



FAB DRAWING



SIZE	QTY	SYM	PLTD
15	231	+	PLTD
70	2	X	NPLTD
95	2	□	PLTD
195	2	◇	PLTD
65	2	⊗	PLTD
20	1	⊗	PLTD

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ±1
2 PLACE ±.01 3 PLACE ±.005
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994

LINEAR TECHNOLOGY

1630 McCarthy Blvd.
Milpitas, CA 95035
PH: (408)432-1900

APPROVALS		TITLE: LTC3723EGN-1, LTC3901EGN,	
DRAWN	INIT	DATE	
CHECK			
DESIGN	JUNE WU	12/5/05	
ENGR	D. Burgoon	12/5/05	
SIZE A		DEMO	DC719A
REV. A		SHT 1 of 1	

SCALE = NONE