



REVISION HISTORY				
ECO	REV	DESCRIPTION	APPR	DATE
-	1	PRODUCTION FAB	GEORGE B.	9-25-15

LAYER STRUCTURE



NOTES: UNLESS OTHERWISE SPECIFIED

- FAB PER IPC-A-600, CLASS 2.
- MATERIAL: -LEAD FREE ASSEMBLY COMPLIANT, ISOLA FR-370HR OR EQUIVALENT.
-FINISHED THICKNESS TO BE 0.031" +/- .005"
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS AND 2 OZ. CU ON THE INNER LAYERS.
-FLAMMABILITY RATING: 94 V-0 MINIMUM.
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
- DRILLING: -DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.001" THICK MIN.
-ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
-HOLE LOCATION TOLERANCES ARE +/-0.003" IN RELATION TO CENTER
- FINISH: -SMOBC USING LPI BOTH SIDES, COLOR GREEN, NO TENT.
-GOLD IMMERSION BOTH SIDES.
(LEAD FREE SOLDER CAN BE USED FOR PROTOTYPE)
-FOR SILKSCREEN: BOTH SIDES USE WHITE NON-CONDUCTIVE INK.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
- PCBS ARE TO BE RoHS COMPLIANT.



SIZE	QTY	SYM	PLATED	TOL
0.01	122	+	YES	+/-0.003"
0.037	4	X	YES	+/-0.003"
0.063	4	X	YES	+/-0.003"
0.187	4	A	YES	+/-0.003"
0.015	3	B	YES	+/-0.003"
0.025	2	C	YES	+/-0.003"
0.094	6	D	YES	+/-0.003"
0.0311	3	E	YES	+/-0.003"
0.031	12	F	YES	+/-0.003"
0.07	2	G	NO	+/-0.003"

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON ANGLE ±1 0.XX" = ±0.01" 0.XXX" = ±0.005" INTERPRET DIM AND TOL PER ASME Y14.5M-1994 THIRD ANGLE PROJECTION 	APPROVALS		 1630 MCCARTHY BLVD MILPITAS, CA 95035 PH: (408)432-1900 www.linear.com LTC CONFIDENTIAL- FOR CUSTOMER USE ONLY
	PCB DES.	NC	
DO NOT SCALE DRAWING	APP ENG.	GEORGE B.	TITLE: FABRICATION DRAWING: 400mA WIRELESS SYNCHRONOUS BUCK BATTERY CHARGER
			SIZE N/A
			IC NO. LTC4120EUD-4.2/LTC4120EUD DEMO CIRCUIT 2445A-A/B
			REV. 1
	SCALE: NONE	FILENAME: DC2445A-1.PCB	SHT 1 of 1