


SIZE	QTY	SYM	PLATED	TOL
0.065	13	+	YES	+/-0.003
0.006	55	X	YES	+/-0.003
0.187	4	□	NO	+/-0.003
0.07	2	◇	NO	+/-0.003
0.01	111	⊗	YES	+/-0.003
0.035	28	⊗ ^A	YES	+/-0.003
0.095	8	⊗ ^B	YES	+/-0.003
0.215	2	⊗ ^B	YES	+/-0.003

ADDITIONAL REQUIREMENT FOR PROTOTYPE FAB ONLY:

1. OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).
- ADDITIONAL REQUIREMENTS FOR PRODUCTION FAB ONLY:


1. PROVIDE COMPLIANCE CERTIFICATES FOR RoHS, REACH AND CONFLICT-FREE MINERALS.
2. SOLDERABILITY BOARD WITH TEST RESULTS.
3. OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).
4. VACUUM PACKED WITH DESICCANT.
5. FULL PANEL WITH NO REJECT.

LAYER STRUCTURE



NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600.
2. MATERIAL: -EPOXY FIBERGLASS, NEMA GRADE FR-4
-FINISHED THICKNESS TO BE 0.062" +/- .005"
-TOTAL OF 4 LAYERS WITH 2 OZ. FINISHED CU ON THE OUTER LAYERS AND 1 OZ. CU ON THE INNER LAYERS.
-FLAMMABILITY RATING: 94 V-0 MINIMUM.
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00" ARE PRIMARY DATUMS.
4. DRILLING: -DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.001" THICK MIN.
-ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
-HOLE LOCATION TOLERANCES ARE +/-0.003" IN RELATION TO CENTER
-FOR VIAS SIZE > 0.01", VIAS HOLES NEED TO BE PLUGGED AND COVERED WITH SOLDERMASK.
5. FINISH: -SMOBC USING LPI BOTH SIDES, COLOR GREEN (GLOSS).
-GOLD IMMERSION BOTH SIDES.
(LEAD FREE SOLDER CAN BE USED FOR PROTOTYPE)
-FOR SILKSCREEN: BOTH SIDES USE WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBS ARE TO BE RoHS COMPLIANT.
8. SCORING FOR PANELIZED PCB:



UNLESS OTHERWISE SPECIFIED		ANALOG DEVICES		POWER BY LINEAR	
DIMENSIONS ARE IN INCHES		www.analog.com			
TOLERANCES:		TITLE: FABRICATION DRAWING			
0.XX" = ±0.01"		I ² C PROGRAMMABLE BOOST			
0.XXX" = ±0.005"		QUAD MONOLITHIC LED DRIVER			
INTERPRET DIM AND TOL PER ASME Y14.5M-1994		SIZE		IC NO.	
THIRD ANGLE PROJECTION		N/A		LT3966EJ	
				DC2630A	
				REV	
				4	
		FILENAME: DC2630A-4.PCB		SHT 1 OF 1	