




REVISION HISTORY				
ECO	REV	DESCRIPTION	APP. ENG.	DATE
-	3	PROD	X. Chen	7-30-19



NOTES: UNLESS OTHERWISE SPECIFIED

1. WORKMANSHIP SHALL BE IN ACCORDANCE WITH PC-A-610.
2. ASSEMBLY PROCESS SHALL INCLUDE REFLOW SOLDER. MAXIMUM SOLDER TEMPERATURE IS 240 DEGREES CELSIUS.
3. PARTS TO OMIT WILL BE SPECIFIED ON THE BILL OF MATERIALS. MARKS OF OMITTED PARTS SHALL BE FREE OF SOLDER. MAKE THE SOLDER STENCIL WHERE SMT PARTS ARE OMITTED.
4. INSTALL SHUNTS AS SHOWN ON ASSY DRAWING.
5. DEPANALIZE BOARDS AFTER ASSEMBLY AND ROUTE-OUT THE BREAKOUT TABS ON FOUR SIDES OF THE BOARD EDGE.
6. DO NOT APPLY ANY KIND OF ASSEMBLY STAMP OR QA STAMP TO ANY BOARD.
7. INSTALL 4 STANDOFFS AT 4 LOCATIONS AS SHOWN BELOW:



APPROVALS		 ANALOG DEVICES 100 TOWER STREET NORFOLK, MA 01950 TEL: (408) 744-0000 FAX: (408) 744-0000 WWW.ANALOG.COM	
POB. DES.	HZ	FOR OUR CUSTOMER USE ONLY	
APP. ENG.	X. Chen	TITLE: TOP ASSEMBLY DRAWING HIGH VOLTAGE DUAL STEP-DOWN DC/DC CONVERTER WITH DIGITAL POWER MANAGEMENT SIZE: IC NO. LTC7880LUK N/A DEMO CIRCUIT 2728A SCALE = NONE FILENAME: DC2728A-3.CBP	
		REV.	3
		SHT. 1 OF 2	