




NOTES: UNLESS OTHERWISE SPECIFIED

1. WORKMANSHIP SHALL BE IN ACCORDANCE WITH IPC-A-610.
2. ASSEMBLY PROCESS SHALL INCLUDE: REFLOW SOLDER TOP SIDE SMD. MAXIMUM SOLDER TEMPERATURE IS 240 DEGREES CELSIUS.
3. PARTS TO OMIT WILL BE SPECIFIED ON THE BILL OF MATERIALS. LOCATIONS OF OMITTED PARTS SHALL BE FREE OF SOLDER. MASK THE SOLDER STENCIL WHERE SMT PARTS ARE OMITTED.
4. INSTALL SHUNTS AS SHOWN ON ASSY DRAWING.
5. DEPANELIZE BOARDS AFTER ASSEMBLY AND ROUTE-OUT THE BREAKOUT TABS ON FOUR SIDES OF THE BOARD EDGE.

6. DO NOT APPLY ANY KIND OF ASSEMBLY STAMP OR QA STAMP TO ANY BOARD.
7. INSTALL 4 STANDOFFS AS SHOWN BELOW:



NOTE
INSTALL COMPONENTS
ON TOP SIDE:
C19, C20, C22, R8, R13
(L3 IS OPT)


PIN1 →  FOOTPRINT
COILCRAFT INDUCTOR

**ANALOG
DEVICES**
www.analog.com

TITLE: TOP ASSEMBLY DRAWING
18V, 8A MONOLITHIC SYNCHRONOUS STEP-DOWN
SILENT SWITCHER 3 WITH LOW NOISE REFERENCE

SIZE N/A	IC NO. LT8625SPEV DC3002A	REV. 4
-------------	---------------------------------	-----------

SHT 1 OF 2



TITLE: BOTTOM ASSEMBLY DRAWING

**18V, 8A MONOLITHIC SYNCHRONOUS STEP-DOWN
SILENT SWITCHER 3 WITH LOW NOISE REFERENCE**

SIZE	IC NO.	REV
N/A	LT8625SPEV DC3002A	4

SHT 2 of 2