



REVISION HISTORY				
ECO	REV	DESCRIPTION	APP. ENG.	DATE
-	01	PRODUCTION	WL	10-14-21

LAYER STRUCTURE

THICKNESS (IN)		
.0005"	SOLDER MASK	
.0028"		TOP LAYER
.012"		PREPREG
.0028"		INNER LAYER
.028"		CORE MATERIAL
.0028"		INNER LAYER
.012"		PREPREG
.0028"		BOTTOM LAYER
.0005"	SOLDER MASK	

NOTES: UNLESS OTHERWISE SPECIFIED

- FABRICATION: FABRICATION AND ACCEPTANCE TO MEET THE REQUIREMENTS OF IPC-A-600 AND IPC/ANSI-MLL950-C CLASS 2, AOL .25 GENERAL INSPECTION LEVEL II.
- MATERIAL: - EPOXY FIBERGLASS, NEMA GRADE FR-4
- FINISHED THICKNESS TO BE 0.062" +/- .005"
- TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE ALL LAYERS
- FLAMMABILITY RATING: 94 V-0 MINIMUM.
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN 0.00" ARE PRIMARY DATUMS.
- DRILLING: - DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.001" THICK MIN.
- ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
- HOLE LOCATION TOLERANCES ARE +/-0.003" IN RELATION TO CENTER.
- FINISH: - SMOBC USING LPI BOTH SIDES, COLOR GREEN. TENT BOTH SIDES.
- GOLD IMMERSION BOTH SIDES.
- FOR SILKSCREEN: BOTH SIDES USE WHITE NON-CONDUCTIVE INK.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
- PCBS ARE TO BE RoHS COMPLIANT.
- SCORING FOR PANELIZED PCB:



SIZE	QTY	SYM	PLATED	TOL
0.01	5	⊕ ^B	YES	+/-0.003
0.011	5	⊕ ^A	YES	+/-0.003
0.012	393	⊕	YES	+/-0.003
0.04	3	⊕ ^E	YES	+/-0.003"
0.065	12	□	YES	+/-0.003"
0.07	2	◇	NO	+/-0.003"
0.095	5	⊗	YES	+/-0.003"
0.19	4	⊗	YES	+/-0.003"
0.205	5	⊗	YES	+/-0.003

ADDITIONAL REQUIREMENT FOR PROTOTYPE FAB ONLY:

- OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).

ADDITIONAL REQUIREMENTS FOR PRODUCTION FAB ONLY:

- PROVIDE COMPLIANCE CERTIFICATES FOR RoHS, REACH AND CONFLICT-FREE MINERALS.
- SOLDERABILITY BOARD WITH TEST RESULTS.
- OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).
- VACUUM PACKED WITH DESICCANT.
- FULL PANEL WITH NO REJECT.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES: 0.XX" = ±0.01" 0.XXX" = ±0.005" INTERPRET DIM AND TOL PER ASME Y14.5M-1994 THIRD ANGLE PROJECTION	APPROVALS		FOR ADI CUSTOMER USE ONLY	
	PCB DES	NC		
	APP ENG	WL	TITLE: FABRICATION DRAWING	
			3.3V TO 1V AT 12.5A, 2MHz AUTOMOTIVE LOW EMI BUCK REGULATOR IN A 1.04cm² SOLUTION	
SCALE = NONE		SIZE N/A		IC NO. LTC3311-1 DEMO CIRCUIT 3113A
				REV 01