



REVISION HISTORY				
ECO	REV	DESCRIPTION	APP. ENG.	DATE
-	2	PRODUCTION	PATRICK W.	06-08-15

SHOWN FROM TOP SIDE




LAYER STRUCTURE



NOTES: UNLESS OTHERWISE SPECIFIED

- FAB PER IPC-A-600.
- MATERIAL: -LEAD FREE ASSEMBLY COMPLIANT, ISOLA FR-370HR OR EQUIVALENT.
-FINISHED THICKNESS TO BE 0.062" +/- .005"
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS AND 1 OZ. CU ON THE INNER LAYERS.
-FLAMMABILITY RATING: 94 V-0 MINIMUM.
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00" ARE PRIMARY DATUMS.
- DRILLING: -DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.001" THICK MIN.
-ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
-HOLE LOCATION TOLERANCES ARE +/-0.003" IN RELATION TO CENTER
- FINISH: -SNOBC USING LPI BOTH SIDES, COLOR GREEN.
-GOLD IMMERSION BOTH SIDES.
-FOR SILKSCREENS: USE WHITE NON-CONDUCTIVE INK.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
- PCBS ARE TO BE RoHS COMPLIANT.
- SCORING FOR PANELIZED PCB (PRODUCTION FAB ONLY):



9. SUBJECT TO CHANGE BY MANUFACTURER, DEPENDING ON DIELECTRIC CONSTANT DEVIATIONS. PLEASE CONSULT LTC.

SIZE	QTY	SYM	PLATED	TOL
0.19	4	+	NO	+/-0.003"
0.07	3	X	NO	+/-0.003"
0.064	18	□	YES	+/-0.003"
0.012	748	◇	YES	+/-0.003"
0.035	32	⊗	YES	+/-0.003"
0.04	42	⊗	YES	+/-0.003"
0.008	95	+ ^A	YES	+/-0.003"
0.189	2	+ ^B	YES	+/-0.003"

UNLESS OTHERWISE SPECIFIED		APPROVALS			
DIMENSIONS ARE IN INCHES TOLERANCES: 0.XX" = ±0.01" 0.XXX" = ±0.005" INTERPRET DIM AND TOL PER ASME Y14.5M-1994 THIRD ANGLE PROJECTION		PCB DES.	KIM T.		
		APP ENG.	PATRICK W.	TITLE: FABRICATION DRAWING POWER, CHARGE AND ENERGY MONITOR WITH INTEGRATED SENSE RESISTOR	
				SIZE	IC NO.
				N/A	LTC2947IUFE
					DEMO CIRCUIT 2334A
		SCALE = NONE		FILENAME: DC2334A-2.PCB	REV 2
					SHT 1 OF 1

1630 MCCARTHY BLVD
MILPITAS, CA 95035
PH: (408)432-1900
WWW.LINEAR.COM
LTC CONFIDENTIAL-
FOR CUSTOMER USE ONLY