



SIZE	QTY	SYM	PLATED	TOL
0.005	10	+ ^A	YES	+/-0.003"
0.008	24	X	YES	+/-0.003"
0.01	57	+ ^B	YES	+/-0.003"
0.035	4	+ ^D	YES	+/-0.003"
0.04	3	+ ^C	YES	+/-0.003"
0.065	11	X	YES	+/-0.003"
0.07	2	□	NO	+/-0.003"
0.095	5	X	YES	+/-0.003"
0.19	4	+	YES	+/-0.003"
0.205	5	◇	YES	+/-0.003"

LAYER STRUCTURE



NOTES: UNLESS OTHERWISE SPECIFIED

- FABRICATION: FABRICATION AND ACCEPTANCE TO MEET THE REQUIREMENTS OF IPC-A-600 AND IPC/ANSI-MLL950-C CLASS 2, AOL .25 GENERAL INSPECTION LEVEL II.
- MATERIAL: - EPOXY FIBERGLASS, NEMA GRADE FR-4
- FINISHED THICKNESS TO BE 0.062" +/- .005"
- TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE ALL LAYERS
- FLAMMABILITY RATING: 94 V-O MINIMUM.
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN 0.00" ARE PRIMARY DATUMS.
- FRONT TO BACK LAYER REGISTRATION.
-SHALL BE WITHIN 0.005" (0.13mm) TO COMPLY WITH IPC-A-600, CLASS 2.
- DRILLING: - DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.001" THICK MIN.
- ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
- HOLE LOCATION TOLERANCES ARE +/-0.003" IN RELATION TO CENTER.
- FINISH: - SMOBC USING LPI BOTH SIDES, PER IPC-SM-840, CLASS T, COLOR GREEN. TENT BOTH SIDES.
- APPLY ELECTROLESS NICKEL GOLD IMMERSION (ENIG) OVER EXPOSED COPPER PER IPC-4552.
- FOR SILKSCREEN: BOTH SIDES USE WHITE NON-CONDUCTIVE INK.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
-PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
- PCBS ARE TO BE RoHS COMPLIANT.
- SCORING FOR PANELIZED PCB:



ADDITIONAL REQUIREMENT FOR PROTOTYPE FAB ONLY:

- OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).

ADDITIONAL REQUIREMENTS FOR PRODUCTION FAB ONLY:

- PROVIDE COMPLIANCE CERTIFICATES FOR RoHS, REACH AND CONFLICT-FREE MINERALS.
- SOLDERABILITY BOARD WITH TEST RESULTS.
- OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).
- VACUUM PACKED WITH DESICCANT.
- FULL PANEL WITH NO REJECT.

REVISION HISTORY				
ECO	REV	DESCRIPTION	APP. ENG.	DATE
-	04	PRODUCTION	MM	07-12-22

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES: 0.XX" = ±0.01" 0.XXX" = ±0.005" INTERPRET DIM AND TOL PER ASME Y14.5M-1994 THIRD ANGLE PROJECTION	APPROVALS		 FOR ADI CUSTOMER USE ONLY
	PCB DES	NC	TITLE: FABRICATION DRAWING 3.3V TO 1.2V AT 6A 2MHz SYNCHRONOUS STEP-DOWN REGULATOR
	APP ENG	MM	
	SIZE	IC NO. LTC3304 DC3203A	REV 04
	N/A		
SCALE = NONE			SHT 1 OF 1