



REVISION HISTORY				
ECO	REV	DESCRIPTION	APP. ENG.	DATE
-	3	PRODUCTION	KH	04-27-18



NOTES: UNLESS OTHERWISE SPECIFIED

1. WORKMANSHIP SHALL BE IN ACCORDANCE WITH IPC-A-610.
2. ASSEMBLY PROCESS SHALL INCLUDE: REFLOW SOLDER TOP SIDE SMD. MAXIMUM SOLDER TEMPERATURE IS 240 DEGREES CELSIUS.
3. PARTS TO OMIT WILL BE SPECIFIED ON THE BILL OF MATERIALS. LOCATIONS OF OMITTED PARTS SHALL BE FREE OF SOLDER. MASK THE SOLDER STENCIL WHERE SMT PARTS ARE OMITTED.
4. DEPANELIZE BOARDS AFTER ASSEMBLY AND ROUTE-OUT THE BREAKOUT TABS ON FOUR SIDES OF THE BOARD EDGE.
5. DO NOT APPLY ANY KIND OF ASSEMBLY STAMP OR QA STAMP TO ANY BOARD.
6. INSTALL 4 STANDOFFS AT AS SHOWN BELOW:



APPROVALS		ANALOG DEVICES POWER BY LINEAR	
PCB DES.	LT	www.linear.com FOR ADI CUSTOMER USE ONLY	
APP ENG.	KH	TITLE: TOP ASSEMBLY DRAWING	
		140V HIGH EFFICIENCY SWITCHING SURGE STOPPER	
		SIZE	IC NO. LTC7862EUFD
		N/A	DEMO BOARD 2674A
SCALE = NONE		FILENAME: DC2674A-3.PCB	REV. 3
			SHT 1 OF 2