


NOTES: UNLESS OTHERWISE SPECIFIED

1. WORKMANSHIP SHALL BE IN ACCORDANCE WITH IPC-A-610.
2. ASSEMBLY PROCESS SHALL INCLUDE: REFLOW SOLDER TOP SIDE SMD. MAXIMUM SOLDER TEMPERATURE IS 240 DEGREES CELSIUS.
3. PARTS TO OMIT WILL BE SPECIFIED ON THE BILL OF MATERIALS. LOCATIONS OF OMITTED PARTS SHALL BE FREE OF SOLDER. MASK THE SOLDER STENCIL WHERE SMT PARTS ARE OMITTED.
4. INSTALL SHUNTS AS SHOWN ON ASSY DRAWING.
5. DEPANELIZE BOARDS AFTER ASSEMBLY AND ROUTE-OUT THE BREAKOUT TABS ON FOUR SIDES OF THE BOARD EDGE.
6. DO NOT APPLY ANY KIND OF ASSEMBLY STAMP OR QA STAMP TO ANY BOARD.
7. INSTALL CONNECTORS, TURRETS, STANDOFFS AS SHOWN BELOW:



8. INSTALL ROHM LED AS SHOWN BELOW:



APPROVALS

PCB DES. J W
APP ENG. K T



TITLE: TOP ASSEMBLY DRAWING

PRIORITIZED POWERPATH CONTROLLER

SIZE N/A IC NO. LTC4417
DC1717B REV. 1

SCALE = NONE

FILENAME: DC1717B-1.PCB

SHT 1 OF 2