
REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09OCT24	I.ANDAL




4-LAYER STACKUP

PRIMARY: 1.600 MM

HOLE TOLERANCE

UNLESS SPECIFIED
PLATED: +/- .0762 MM
NON PLATED: +/- .0508 MM

DRILL CHART: TOP to BOTTOM				
ALL UNITS ARE IN MILLIMETERS				
FIGURE	SIZE	PLATED	QTY	TOLERANCE/NOTES
·	0.127	PLATED	38	DIA MAX SEE NOTE #20
▫	0.2032	PLATED	563	DIA MAX SEE NOTE #20
○	1.016	PLATED	32	
◦	1.143	PLATED	62	
◇	1.1684	PLATED	2	
○	1.27	PLATED	2	
△	1.6002	PLATED	15	
○	1.7018	PLATED	8	
A	0.6604	NON-PLATED	2	
B	3.175	NON-PLATED	2	
0	1.397x0.6096	PLATED	2	
0	1.7018x0.6096	PLATED	2	



PRIMARY SIDE

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MM TOLERANCES DECIMALS FRACTIONS ANGLES .XX +-.010 +-1/32 +- 2 .XXX +-.005 .XXXX +-.0050	APPROVAL	DATE
	TEMPLATE ENGINEER	
	HARDWARE SERVICES M.VALE	09OCT24
	HARDWARE SYSTEMS	
MATERIAL	TEST ENGINEER	
	COMPONENT ENGINEER K.EMPENSANDO	13SEP24
	TEST PROCESS	
	HARDWARE RELEASE K.JABATAN	09OCT24
FINISH	DESIGNER J.PANGANIBAN	09OCT24
	PTD ENGINEER I.ANDAL	09OCT24
	CHECKER	
DO NOT SCALE DWG		

ANALOG DEVICES

WWM
DIVISION
804 WOBURN STREET
WILMINGTON, MA 01887

TITLE

FABRICATION
EVAL-AD3531RARDZ
CUSTOMER EVAL Z

SIZE	FSCM NO	DRAWING NUMBER	REV
C	24355	09-084207	A

SCALE 1/1 SHEET 1 OF 2

NOTES: UNLESS OTHERWISE SPECIFIED

1. DIMENSIONS ARE IN MM (EXCEPT WHERE NOTED).
ALL DOCUMENTS & SPECIFICATIONS REFERRED TO BELOW SHOULD BE THE LATEST REVISIONS.

MATERIAL: HOMOGENOUS MATERIALS IN THIS BOARD SHALL BE COMPLAINT WITH THE EU DIRECTIVE 2002/95/EC

2. BOARD MATERIAL:(USE CHECKED ITEMS)

(X) ISOLA 370HR OR EQUIVALENT
( ) ISOLA-FR408HR OR EQUIVALENT
( ) ISOLA IS410
( ) MEGTRON 6
( ) NELCO-4000-13
( ) ROGERS 4350B
( ) ROGERS 3003
( ) ARLON 85N
( ) EM370D
( ) OTHER _____

3. ALL LAMINATES & BONDING MATERIALS SHOULD BE SELECTED FROM IPC-4101 OR IPC-4103,(TG>170 DEGC TD>300 DEGC)
UL FLAMMABILITY RATING 94V-0. BOARD MATERIAL & CONSTRUCTION SHALL MEET THE REQUIREMENTS OF UL796/UL796F.
4. REFER TO IPC-6010 SERIES, CLASS 2 FOR FABRICATION.WORKMANSHIP SHALL CONFORM TO IPC-A-600, CLASS 2.
5. REFER TO LAMINATION DIAGRAM FOR OVERALL BOARD THICKNESS, TOLERANCE APPLIES AFTER ALL LAMINATION AND PLATING PROCESSES. FINISHED THICKNESS MEASURED FROM TOP COPPER TO BOTTOM COPPER.
6. BOW & TWIST NOT TO EXCEED 0.0075 INCHES (0.75%) PER LINEAR INCH AND SHOULD BE MEASURED PER IPC-TM-650, METHOD 2.4.22.
7. ACCEPTABILITY PER ADI SPECIFICATION TST00115.

TOOLING:

8. IMPEDANCE REQUIREMENTS: IF NO STACKUP IS DEFINED, THE VENDOR IS ALLOWED TO ADJUST THE DIELECTRIC THICKNESS & TRACE WIDTHS TO MEET THE IMPEDANCE REQUIREMENT. IF SPECIFIED, THE VENDOR MUST MEET THE REQUIREMENTS LISTED IN THE IMPEDANCE TABLE. ANY ADJUSTMENT MADE TO THE DEFINED STACKUP, TRACE WIDTH & SPACING THAT IMPACT THE REQUIREMENTS MUST HAVE WRITTEN APPROVAL FROM ADI.
9. FILLET OPTIONS TO ENHANCE RELIABILITY AT PAD JUNCTIONS WHERE SPACING PERMITS.
( ) FILLETS ALLOWED
(X) FILLETS NOT ALLOWED
10. THIEVING:
( ) VENDOR MAY ADD THIEVING TO COMPENSATE FOR LOW COPPER DENSITY AREAS MAINTAINING A MINIMUM 2.54 MM CLEARANCE FROM ALL COPPER FEATURES,
(X) VENDOR MAY NOT ADD THIEVING TO COMPENSATE FOR LOW COPPER DENSITY AREAS.
11. LAYER TO LAYER REGISTRATION SHALL BE WITHIN 0.0762 MM.

FINISH:

12. DRILL SIZES ARE FINISHED HOLE SIZES. ALL HOLES SHALL BE LOCATED WITHIN 0.127 MM DTP, MINIMUM BARREL PLATING OF 0.0254 MM. PLATED HOLES SHALL NOT BE ROUGH OR IRREGULAR SO AS TO HINDER PROPER SOLDER WICKING. BARREL RELIEF ON SOLDERMASK ALLOWED IN UNFILLED VIA IN PAD HOLES.
13. PLATING SPECIFICATION:
(X) REFER TO LAMINATION DIAGRAM FOR FINISHED COPPER WEIGHT/THICKNESS REQUIRMENTS
THE STARTING COPPER WEIGHT/THICKNESS CAN VARY AS LONG AS THE FINISHED COPPER WEIGHT/THICKNESS IS NOT LESS THAN THE SPECIFIED VALUE.
14. SURFACE FINISH:

(X) IMMERSION GOLD (ENIG) 1.58-3.94 MICRO INCHES OVER 118-236 MICRO INCHES MIN. OF ELECTROLESS NICKEL PER IPC-4552
( ) OSP (ORGANIC SOLDERABILITY PRESERVATIVE)
( ) IMMERSION SILVER
( ) SOFT WIRE BONDABLE GOLD 30-50 MICRO INCHES OF SOFT WIRE BONDABLE GOLD OVER 100-150 MICRO INCHES OF NICKEL
( ) EDGE CONNECTOR FINGERS ARE TO BE PLATED WITH 100 MICRO-INCHES(.0001") OF LOW STRESS NICKEL UNDER 30 MICRO-INCHES (.0003') OF GOLD
( ) OTHER_____

15. SOLDERMASK:

SOLDERMASK OVER BARE COPPER OR BARE GOLD (BOTH SIDES) TO MEET IPC-SM-840.
IF PRESENT,DO NOT MODIFY SOLDERMASK DEFINED PADS (MASK OPENINGS LESS THAN COPPER PAD) WITHOUT APPROVAL.
(X) LPI
( ) OTHER_____

COLOR
(X) GREEN
( ) OTHER_____

16. APPLY SILKSCREEN TO BOTH SIDES USING A NON-CONDUCTIVE, EPOXY BASED INK PER ARTWORK.
(X) WHITE
( ) OTHER

TESTING:

17. FINAL ELECTRICAL TEST TO BE PERFORMED USING PROVIDED IPC-D-356A NETLIST OR ODB++ FORMAT FILE. THE PCB SHALL HAVE A VERIFICATION STAMP.
18. A TIME DOMAIN REFLECTOMETER REPORT (TDR) FOR EACH IMPEDANCE CONTROLLED LAYER & A CERTIFICATE OF COMPLIANCE SHALL BE PROVIDED BY VENDOR AT TIME OF SHIPMENT. INSTANCES WHERE TDR TESTING CAN'T BE PERFORMED BECAUSE THE TRACE LENGTH IS TOO SHORT ON THE OUTER LAYERS AT THE PIN ESCAPES IS ACCEPTABLE, ALL OTHER INSTANCES MUST BE REPORTED.

MISCELLANEOUS:

19. IF PRESENT, ALL BLIND/BURIED VIAS WITH AN ASPECT RATIO <1:1 TO BE PLATED SHUT WITH COPPER WHEN USED AS VIA-IN-PAD OR AS A STACKED VIA. BLIND/BURIED VIAS WITH AN ASPECT RATIO >1:1 TO BE FILLED WITH NON-CONDUCTIVE EPOXY.
20. FOR VIA FILL INFORMATION REFER TO DRILL CHART:
(X) NON-CONDUCTIVE EPOXY FILL DRILLED VIAS
( ) COPPER FILL DRILLED VIAS
21. INTENTIONAL SHORTS:
IF AN INTENTIONAL SHORT REPORT IS SUPPLIED AND DOES NOT MATCH THE FAB DATA THEN ADI APPROVAL IS REQUIRED.
22. PEMNUTS:
( ) PEMNUTS TO BE INSTALLED BY FABRICATOR
( ) PEMNUTS NOT TO BE INSTALLED BY FABRICATOR
(X) NOT APPLICABLE
23. MANUFACTURER TO ETCH/STAMP WITH PERMANENT NON-CONDUCTIVE INK ON SECONDARY SIDE UNLESS OTHERWISE SPECIFIED:
A. UL CODE-FLAMMABILITY RATING FOR THOSE APPROVED MATERIALS(IF APPLICABLE)
B. DATE CODE
C. LOT NUMBER
D. MANUFACTURER LOGO
24. PANELIZATION:
BOARDS TO BE SHIPPED IN ARRAY AND KEPT INTACT
PANEL TO BE SUBJECTED TO CUSTOMERS APPROVAL
PANEL SOLDER PASTE STENCIL GERBER TO BE PROVIDED TO ANALOG
25. MINIMUM DESIGN LINE WIDTH IS .1524MM.
26. MINIMUM DESIGN LINE SPACING IS .0796 MM.

FAB NOTES REVISION: 2ND NOVEMBER 2022

PRIMARY SIDE

ANALOG DEVICES
WWM
DIVISION
804 WOBURN STREET
WILMINGTON, MA 01887

SIZE	FSCM NO	DRAWING NUMBER	REV
C	24355	09-084207	A
SCALE 1/1			SHEET 2 OF 2

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09OCT24	I.ANDAL

ASSEMBLY NOTES:

1. BOARD ACCEPTABILITY PER ANALOG DEVICES, INC. SPECIFICATION TST00119 (LATEST REVISION).

2. REPAIRS PER IPC-7711/21(LATEST REVISION) ARE ALLOWED.


3. REPAIRS ARE NOT ALLOWED IN SOLDERMASK FREE AREAS ON EITHER SIDE OF THE BOARD.

4. RoHS COMPLIANCE: ASSEMBLY VENDOR SHOULD ASSURE COMPLIANCE WITH LEAD-FREE AND RoHS PCB ASSEMBLY STANDARDS (EU RoHS DIRECTIVE 2002/95/EC).

5. BOARDS TO BE SHIPPED SINGULATED AFTER ASSEMBLY PROCESS. SMOOTHEN EDGES AND FREE FROM BURRS AFTER DEPANELIZATION PROCESS.


6. DO NOT TRIM EXCESS TAIL LENGTH:
   P1, P2, P4 & P9

7. JUMPER SHUNT (MPN: SNT-100-BK-G-H) DEFAULT SETTINGS:
   SHORT: JP1: (PIN1 & PIN2), JP3: (PIN1 & PIN2)
   SHORT: JP2 , JP5
   OPEN: JP4
   NOTE: INCLUDE THE UNINSTALLED SHUNTS DURING SHIPMENT



PRIMARY SIDE

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MM	APPROVAL	DATE	
TOLERANCES DECIMALS .XX +-.010 .XXX +-.005 .XXXX +-.0050 FRACTIONS +-1/32 ANGLES +- 2	TEMPLATE ENGINEER		ANALOG DEVICES WWM DIVISION 804 WOBURN STREET WILMINGTON, MA 01887
	HARDWARE SERVICES M.VALE	09OCT24	
	HARDWARE SYSTEMS		TITLE ASSEMBLY EVAL-AD3531RARDZ CUSTOMER EVAL Z
MATERIAL	TEST ENGINEER		
	COMPONENT ENGINEER K.EMPENSANDO	13SEP24	
	TEST PROCESS		
	HARDWARE RELEASE K.JABATAN	09OCT24	
FINISH	DESIGNER J.PANGANIBAN	09OCT24	SIZE: C / FSCM NO: 24355 / DRAWING NUMBER: 01-084207 / REV: A
	PTD ENGINEER I.ANDAL	09OCT24	
	CHECKER		
DO NOT SCALE DWG			SCALE 1/1 / SHEET 1 OF 2




SECONDARY SIDE


ANALOG DEVICES
WWM
DIVISION
804 WOBURN STREET
WILMINGTON, MA 01887

SIZE	FSCM NO	DRAWING NUMBER	REV
C	24355	01-084207	A
SCALE 1/1			SHEET 2 OF 2


L1 PRIMARY
08-084207-01
REV A




L2 GND
08-084207-07
REV A




L3 PWR
08-084207-08
REV A




L4 SECONDARY
08-084207-02
REV A




SILKSCREEN PRIMARY
08-084207-03
REV A




SOLDERMASK PRIMARY
08-084207-04
REV A




SILKSCREEN SECONDARY
08-084207-05
REV A



SOLDERMASK SECONDARY
08-084207-06
REV A



PASTEMASK PRIMARY
08-084207-09
REV A



PASTEMASK SECONDARY
08-084207-10
REV A

