

LINEAR TECHNOLOGY MATERIALS DECLARATION

1t1227cs8#pbf		(Engineering Calculation)				SOIC
(printed on: 2020-07-11 20:05:53)					TOTAL MASS (g) : 0.072194	
COMPONENT MATERIAL	VENDOR/ INDUSTRY NAMES	CONSTITUENT NAME	CAS NUMBER	CONSTITUENT MASS (g)	CONSTITUENT (PPM) OF MATERIAL	CONSTITUENT (PPM) OF TOTAL PKG.
Active Device	Linear Technology	Silicon (Si)	7440-21-3	0.001232	1000000	17065.1640625
Die Coat	Dow Corning	Silicone	69430-27-9	0.000000	0	0
Lead Frame	Cu	Copper (Cu)	7440-50-8	0.023653	975000	327631.78125
		Iron (Fe)	7439-89-6	0.000582	24000	8061.62792969
		Phosphorus (P)	7723-14-0	0.000007	300	96.9611663818
		Zinc (Zn)	7440-66-6	0.000017	700	235.477111816
		Nickel (Ni)	7440-02-0	0.000000	0	0
		Silicon (Si)	7440-21-3	0.000000	0	0
		Magnesium (Mg)	7439-95-4	0.000000	0	0
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead Frame Total:		0.024259	1000000	336025.84375
Plating	PMI	Exter. Plating Pb	7439-92-1	0.000000	0	0
		Exter. Plating Sn	7440-31-5	0.001477	1000000	20456.7558594
		External Plating Total:		0.001477	1000000	20456.7558594
		Inter. Plating Ni	7440-02-0	0.000000	0	0
		Inter. Plating Ag	7440-22-4	0.000068	1000000	941.908447266
		Internal Plating Total:		0.000068	1000000	941.908447266
Die Attach	ELECTRICALLY CONDUCTIVE ADHESIVE	Silver (Ag)	7440-22-4	0.000501	750000	6939.6484375
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead (Pb)	7439-92-1	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.000000	0	0
		Indium (In)	7440-74-6	0.000000	0	0
		Metal Oxide		0.000000	0	0
		Antimony (Sb)	7440-36-0	0.000000	0	0
		Resin (EP)		0.000167	250000	2313.21655273
		Die Attach Total:		0.000668	1000000	9252.86621094
Encapsulation	MULTI-AROMATIC RESIN Br/Sb FREE	Resin (EP)		0.006657	150000	92210.0703125
		Bromine (Br)	40039-93-8	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.036392	820000	504087.21875
		Antimony Trioxide (Sb2O3)	1309-64-4	0.000000	0	0
		Metal Hydroxide		0.001110	25000	15375.2695312
		Carbon Black (C)	1333-86-4	0.000222	5000	3075.05419922
		Encapsulation Total:		0.044381	1000000	614747.625
Bond Wire Estimated	AFW/TANAKA/ Kn	Gold (Au)	7440-57-5	0.000109	1000000	1509.82385254
					TOTAL MASS (g) :	0.072194