

LINEAR TECHNOLOGY MATERIALS DECLARATION

1t1815cs5#trpbf

(Engineering Calculation)

TSOT-23

(printed on: 2020-07-11 18:46:46)

TOTAL MASS (g) : 0.012434

COMPONENT MATERIAL	VENDOR/ INDUSTRY NAMES	CONSTITUENT NAME	CAS NUMBER	CONSTITUENT MASS (g)	CONSTITUENT (PPM) OF MATERIAL	CONSTITUENT (PPM) OF TOTAL PKG.
Active Device	Linear Technology	Silicon (Si)	7440-21-3	0.000559	1000000	44956.5234375
Die Coat	Dow Corning	Silicone	69430-27-9	0.000000	0	0
Lead Frame	Cu	Copper (Cu)	7440-50-8	0.004485	975000	360697.6875
		Iron (Fe)	7439-89-6	0.000110	24000	8846.54296875
		Phosphorus (P)	7723-14-0	0.000001	300	80.4231185913
		Zinc (Zn)	7440-66-6	0.000003	700	241.269363403
		Nickel (Ni)	7440-02-0	0.000000	0	0
		Silicon (Si)	7440-21-3	0.000000	0	0
		Magnesium (Mg)	7439-95-4	0.000000	0	0
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead Frame Total:		0.004599	1000000	369865.90625
Plating	PMI	Exter. Plating Pb	7439-92-1	0.000000	0	0
		Exter. Plating Sn	7440-31-5	0.000635	1000000	51087.6328125
		External Plating Total:		0.000635	1000000	51087.6328125
		Inter. Plating Ni	7440-02-0	0.000000	0	0
		Inter. Plating Ag	7440-22-4	0.000080	1000000	6433.84912109
		Internal Plating Total:		0.000080	1000000	6433.84912109
Die Attach	ELECTRICALLY CONDUCTIVE ADHESIVE	Silver (Ag)	7440-22-4	0.000408	750000	32812.6328125
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead (Pb)	7439-92-1	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.000000	0	0
		Indium (In)	7440-74-6	0.000000	0	0
		Metal Oxide		0.000000	0	0
		Antimony (Sb)	7440-36-0	0.000000	0	0
		Resin (EP)		0.000136	250000	10937.5449219
		Die Attach Total:		0.000544	1000000	43750.1796875
Encapsulation	MULTI-AROMATIC RESIN Br/Sb FREE	Resin (EP)		0.000775	130000	62327.9179688
		Bromine (Br)	40039-93-8	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.004947	830000	397853.15625
		Antimony Trioxide (Sb2O3)	1309-64-4	0.000000	0	0
		Metal Hydroxide		0.000209	35000	16808.4316406
		Carbon Black (C)	1333-86-4	0.000030	5000	2412.69335938
		Encapsulation Total:		0.005961	1000000	479402.21875
Bond Wire Estimated	AFW/TANAKA/ Kn	Gold (Au)	7440-57-5	0.000056	1000000	4503.69482422
					TOTAL MASS (g) :	0.012434