

SIZE	QTY	SYM	PLATED	TOL
0.187	4	+	NO	+/-0.003
0.094	16	X	YES	+/-0.003
0.01	807	□	YES	+/-0.003
0.07	2	◇	NO	+/-0.003
0.035	40	⊗	YES	+/-0.003
0.215	6	⊗	YES	+/-0.003
0.006	36	+ ^A	YES	+/-0.003
0.065	6	+ ^B	YES	+/-0.003

ADDITIONAL REQUIREMENT FOR PROTOTYPE FAB ONLY:

1. OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).

ADDITIONAL REQUIREMENTS FOR PRODUCTION FAB ONLY:

1. PROVIDE COMPLIANCE CERTIFICATES FOR RoHS, REACH AND CONFLICT-FREE MINERALS.


2. SOLDERABILITY BOARD WITH TEST RESULTS.

3. OUTGOING INSPECTION REPORT (BASED ON ACTUAL MEASUREMENTS AND CROSS SECTION).

4. VACUUM PACKED WITH DESICCANT.


5. FULL PANEL WITH NO REJECT.


LAYER STRUCTURE



NOTES: UNLESS OTHERWISE SPECIFIED

- FAB PER IPC-A-600.
- MATERIAL: -EPOXY FIBERGLASS, NEMA GRADE FR-4
-FINISHED THICKNESS TO BE 0.062" +/- .005"
-TOTAL OF 4 LAYERS WITH 2 OZ. FINISHED CU ON ALL LAYERS.
-FLAMMABILITY RATING: 94 V-0 MINIMUM.
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00" ARE PRIMARY DATUMS.
- DRILLING: -DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.001" THICK MIN.
-ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
-HOLE LOCATION TOLERANCES ARE +/-0.003" IN RELATION TO CENTER
-FOR VIAS SIZE > 0.01", VIAS HOLES NEED TO BE PLUGGED AND COVERED WITH SOLDERMASK.
- FINISH: -SMOBC USING LPI BOTH SIDES, COLOR GLOSS TEAL
-GOLD IMMERSION BOTH SIDES.
(LEAD FREE SOLDER CAN BE USED FOR PROTOTYPE)
-FOR SILKSCREEN: BOTH SIDES USE WHITE NON-CONDUCTIVE INK.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
- PCBS ARE TO BE RoHS COMPLIANT.
- SCORING FOR PANELIZED PCB:



UNLESS OTHERWISE SPECIFIED		 ANALOG DEVICES www.analog.com	
DIMENSIONS ARE IN INCHES		TITLE: FABRICATION DRAWING 42V,QUAD GANGABLE, MONOLITHIC STEP-DOWN REGULATOR	
TOLERANCES:			
0.XX" = ±0.01"			
0.XXX" = ±0.005"			
INTERPRET DIM AND TOL PER ASME Y14.5M-1994			
THIRD ANGLE PROJECTION			
