

87654321

REVISION:H00

| | | | |
|-----|-----------------|--------|----------|
| REV | DESCRIPTION | DATE | APPROVED |
| X | INITIAL RELEASE | ddMMyy | X |

ANALOG
DEVICES

HARDWARE NAME: EVAL-RHP50000-CSLZ

HARDWARE NUMBER: BR-100211

ENGINEER: J. GONZALES

DESIGNER: M. VALE

DATE: 07/4/2025

ODB++/GERBER: FAB NOTES

ALL RIGHTS RESERVED. INFORMATION CONTAINED HEREIN IS PROPRIETARY AND CONFIDENTIAL TO ANALOG DEVICES. NO PART OF THIS DOCUMENT MAY BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT PERMISSION FROM ANALOG DEVICES.

NOTES : UNLESS OTHERWISE SPECIFIED

1. DIMENSIONS ARE IN INCHES (EXCEPT WHERE NOTED).

ALL DOCUMENTS & SPECIFICATIONS REFERRED TO BELOW SHOULD BE THE LATEST REVISIONS.

MATERIAL : HOMOGENOUS MATERIALS IN THIS BOARD SHALL BE COMPLIANT WITH THE EU RoHS DIRECTIVE 2002/95/EC

(USE CHECKED ITEMS)

2. BOARD MATERIAL :

☒ ISOLA 370HR OR EQUIVALENT

☐ ISOLA-FR408HR OR EQUIVALENT

☐ ISOLA IS410

☐ MEGTRON 6

☐ NELCO-4000-13

☐ ROGERS 4350B

☐ ROGERS 3003

☐ OTHER _____

3. ALL LAMINATES & BONDING MATERIALS SHOULD BE SELECTED FROM IPC-4101 OR IPC-4103.(TG>170 DEGC TD>300 DEGC)

UL FLAMMABILITY RATING 94V-0. BOARD MATERIAL & CONSTRUCTION SHALL MEET THE REQUIREMENTS OF UL796/UL796F.

4. REFER TO IPC-6010 SERIES, CLASS 2 FOR FABRICATION.WORKMANSHIP SHALL CONFORM TO IPC-A-600, CLASS 2.

5. REFER TO LAMINATION DIAGRAM FOR OVERALL BOARD THICKNESS, TOLERANCE APPLIES AFTER ALL LAMINATION AND PLATING PROCESSES. FINISHED THICKNESS MEASURED FROM TOP COPPER TO BOTTOM COPPER.

6. BOW & TWIST NOT TO EXCEED 0.0075 INCHES (0.75%) PER LINEAR INCH AND SHOULD BE MEASURED PER IPC-TM-650, METHOD 2.4.22.

7. ACCEPTABILITY PER ADI SPECIFICATION TST00115.

TOOLING :

8. IMPEDANCE REQUIREMENTS: IF NO STACKUP IS DEFINED, THE VENDOR IS ALLOWED TO ADJUST THE DIELECTRIC THICKNESS & TRACE WIDTHS TO MEET THE IMPEDANCE REQUIREMENT. IF SPECIFIED, THE VENDOR MUST MEET THE REQUIREMENTS LISTED IN THE IMPEDANCE TABLE. ANY ADJUSTMENT MADE TO THE DEFINED STACKUP, TRACE WIDTH & SPACING THAT IMPACT THE REQUIREMENTS MUST HAVE WRITTEN APPROVAL FROM ADI.

9. FILLET OPTIONS TO ENHANCE RELIABILITY AT PAD JUNCTIONS WHERE SPACING PERMITS.

☐ FILLETS ALLOWED

☒ FILLETS NOT ALLOWED

10. THIEVING:

☐ VENDOR MAY ADD THIEVING TO COMPENSATE FOR LOW COPPER DENSITY AREAS MAINTAINING A MINIMUM 0.100 INCH CLEARANCE FROM ALL COPPER FEATURES.

☒ VENDOR MAY NOT ADD THIEVING TO COMPENSATE FOR LOW COPPER DENSITY AREAS.

11. LAYER TO LAYER REGISTRATION SHALL BE WITHIN 0.003 INCHES.

FINISH :

12. DRILL SIZES ARE FINISHED HOLE SIZES. ALL HOLES SHALL BE LOCATED WITHIN 0.005 INCHES DTP,UNLESS SPECIFIED. MINIMUM BARREL PLATING OF 0.001 INCHES. PLATED HOLES SHALL NOT BE ROUGH OR IRREGULAR SO AS TO HINDER PROPER SOLDER WICKING. BARREL RELIEF ON SOLDERMASK ALLOWED IN UNFILLED VIA IN PAD HOLES.

13. PLATING SPECIFICATION:

☒ REFER TO LAMINATION DIAGRAM FOR FINISHED COPPER WEIGHT/THICKNESS REQUIRMENTS

THE STARTING COPPER WEIGHT/THICKNESS CAN VARY AS LONG AS THE FINISHED COPPER WEIGHT/THICKNESS IS NOT LESS THAN THE SPECIFIED VALUE.

14. SURFACE FINISH:

☒ IMMERSION GOLD (ENIG) 1.58-3.94 MICRO INCHES OVER 118-236 MICRO INCHES MIN. OF ELECTROLESS NICKEL PER IPC-4552

☐ OSP (ORGANIC SOLDERABILITY PRESERVATIVE)

☐ IMMERSION SILVER

☐ SOFT WIRE BONDABLE GOLD 30-50 MICRO INCHES OF SOFT WIRE

BONDABLE GOLD OVER 100-150 MICRO INCHES OF NICKEL

☐ EDGE CONNECTOR FINGERS ARE TO BE PLATED WITH 100 MICRO-INCHES(.0001") OF LOW STRESS NICKEL UNDER 30 MICRO-INCHES (.0003") OF GOLD

15. SOLDERMASK:

SOLDERMASK OVER BARE COPPER OR BARE GOLD (BOTH SIDES) TO MEET IPC-SM-840.

IF PRESENT,DO NOT MODIFY SOLDERMASK DEFINED PADS (MASK OPENINGS LESS THAN COPPER PAD) WITHOUT APPROVAL.

☒ LPI

☐ OTHER_____

COLOR

☒ GREEN

☐ OTHER_____

16. APPLY SILKSCREEN TO BOTH SIDES USING A NON-CONDUCTIVE, EPOXY BASED INK PER ARTWORK.

☒ WHITE

☐ OTHER_____

TESTING :

17. FINAL ELECTRICAL TEST TO BE PERFORMED USING PROVIDED IPC-D-356A NETLIST OR ODB++ FORMAT FILE. THE PCB SHALL HAVE A VERIFICATION STAMP.

18. A TIME DOMAIN REFLECTOMETER REPORT (TDR) FOR EACH IMPEDANCE CONTROLLED LAYER & A CERTIFICATE OF COMPLIANCE SHALL BE PROVIDED BY VENDOR AT TIME OF SHIPMENT. INSTANCES WHERE TDR TESTING CAN'T BE PERFORMED BECAUSE THE TRACE LENGTH IS TOO SHORT ON THE OUTER LAYERS AT THE PIN ESCAPES

☐ OTHER _____

MISCELLANEOUS :

19. IF PRESENT, ALL BLIND/BURIED VIAS WITH AN ASPECT RATIO <1:1 TO BE PLATED SHUT WITH COPPER WHEN USED AS VIA-IN-PAD OR AS A STACKED VIA. BLIND/BURIED VIAS WITH AN ASPECT RATIO >1:1 TO BE FILLED WITH NON-CONDUCTIVE EPOXY.

20. FOR VIA FILL INFORMATION REFER TO DRILL CHART:

☒ NON-CONDUCTIVE EPOXY FILL ALL DRILLED VIAS

☐ COPPER FILL ALL 0.XXXX INCHES DRILLED VIAS

21. INTENTIONAL SHORTS:

IF AN INTENTIONAL SHORT REPORT IS SUPPLIED AND DOES NOT MATCH THE FAB DATA THEN ADI APPROVAL IS REQUIRED.

22. PEMNUTS:

☐ PEMNUTS TO BE INSTALLED BY FABRICATOR..

☐ PEMNUTS NOT TO BE INSTALLED BY FABRICATOR.

☒ NOT APPLICABLE.

23. MANUFACTURER TO ETCH/STAMP WITH PERMANENT NON-CONDUCTIVE INK ON BOTTOM LEGEND LAYER. CREATE BOTTOM LEGEND IF LAYER NOT PRESENT.

A. UL CODE-FLAMMABILITY RATING FOR THOSE APPROVED MATERIALS(IF APPLICABLE)

B. DATE CODE

C. LOT NUMBER

D. MANUFACTURER LOGO

FAB NOTES REVISION: FEBRUARY 21 2025

LAMINATION DIAGRAM

| LAYER NUMBER | LAYER NAME | COPPER THICKNESS (OZ, INCH) | DIELECTRIC THICKNESS (INCH) | MATERIALS |
|--------------|------------|-----------------------------|------------------------------|------------------------------------|
| 1 | TOP | 2 OZ, 0.0028" MIN | | FINAL CU (THICKNESS AFTER PLATING) |
| | | | .012 | ISOLA 370HR/EQUIVALENT |
| 2 | INTERNAL2 | 2 OZ, 0.0028" MIN | | CU CLAD |
| | | | .028 | ISOLA 370HR/EQUIVALENT |
| 3 | INTERNAL3 | 2 OZ, 0.0028" MIN | | CU CLAD |
| | | | .012 | ISOLA 370HR/EQUIVALENT |
| 4 | BOTTOM | 2 OZ, 0.0028" MIN | | FINAL CU (THICKNESS AFTER PLATING) |

THE FINISHED PCB THICKNESS TO BE: 0.0625" +/-0.010"

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO ADI. THE INFORMATION IN THIS DOCUMENT IS NOT TO BE SHOWN, REPRODUCED, OR DISCUSSED TO ANYONE OUTSIDE OF ADI WITHOUT PRIOR WRITTEN PERMISSION FROM ADI.

ANALOG
DEVICES

TITLE

FABRICATION
EVAL-RHP50000-CSLZ

| | | | | | |
|-------------------------|---------|-------|--|----------------|--------------|
| DESIGNER | DATE | SIZE | UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES | DRAWING NUMBER | REV |
| DESIGNER M. VALE | 40725 | | | | |
| ENGINEER J. GONZALES | 40725 | D | DRAWINGS DECIMALS FRACTIONS ANGLES TYPICAL UNLESS OTHERWISE SPECIFIED | 09-100211 | A |
| APPROVAL J. GONZALES | 30JUN25 | | | | |
| DO NOT SCALE DWG | | SCALE | 1/1 | TEMPLATE REV: | SHEET 2 OF 2 |



This document contains information considered proprietary, and shall not be reproduced wholly or in part, nor disclosed to others without specific written permission.

HARDWARE NAME: EVAL-RHP50000-CSLZ


HARDWARE NUMBER: BR-100211

ENGINEER: J. GONZALES

DESIGNER: M. VALE

DATE: 07/4/2025

ODB++/GERBER: TOP





This document contains information considered proprietary, and shall not be reproduced wholly or in part, nor disclosed to others without specific written permission.

HARDWARE NAME: EVAL-RHP50000-CSLZ


HARDWARE NUMBER: BR-100211

ENGINEER: J. GONZALES

DESIGNER: M. VALE

DATE: 07/4/2025

ODB++/GERBER: INTERNAL2





This document contains information considered proprietary, and shall not be reproduced wholly or in part, nor disclosed to others without specific written permission.

HARDWARE NAME: EVAL-RHP50000-CSLZ


HARDWARE NUMBER: BR-100211

ENGINEER: J. GONZALES

DESIGNER: M. VALE

DATE: 07/4/2025

ODB++/GERBER: INTERNAL3





This document contains information considered proprietary, and shall not be reproduced wholly or in part, nor disclosed to others without specific written permission.

HARDWARE NAME: EVAL-RHP50000-CSLZ


HARDWARE NUMBER: BR-100211

ENGINEER: J. GONZALES

DESIGNER: M. VALE

DATE: 07/4/2025

ODB++/GERBER: BOTTOM





This document contains information considered proprietary, and shall not be reproduced wholly or in part, nor disclosed to others without specific written permission.

HARDWARE NAME: EVAL-RHP50000-CSLZ


HARDWARE NUMBER: BR-100211

ENGINEER: J. GONZALES

DESIGNER: M. VALE

DATE: 07/4/2025

ODB++/GERBER: MASK_TOP





This document contains information considered proprietary, and shall not be reproduced wholly or in part, nor disclosed to others without specific written permission.

HARDWARE NAME: EVAL-RHP50000-CSLZ


HARDWARE NUMBER: BR-100211

ENGINEER: J. GONZALES

DESIGNER: M. VALE


DATE: 07/4/2025

ODB++/GERBER: MASK_BOT





ODB++/GERBER:SILK TOP





ANALOG
DEVICES

This document contains information considered proprietary,
and shall not be reproduced wholly or in part,
nor disclosed to others without specific written permission.

HARDWARE NAME:EVAL-RHP50000-CSLZ

HARDWARE NUMBER:BR-100211

ENGINEER:J. GONZALES

DESIGNER:M. VALE

DATE: 07/4/2025

ODB++/GERBER:SILK_BOT

| MODE | R3 | R4 | R5 | R7 |
|-------------|------|---------|--------------|-------------------|
| FORCED CONT | OPEN | OR OPEN | POPULATED OR | POPULATED OR OPEN |
| PULSE SKIP | 100K | 0 | OPEN | OPEN |

***MODE/2VSYNC PIN 12 CLOCK OUTPUT WHEN R3 IS POPULATED
*IF R3 IS POPULATED R4 MUST BE OPEN

R2
R1

C18

FOR ADI CUSTOMER USE ONLY
08-100511 REV A 1
SECONDARY SIDE



This document contains information considered proprietary, and shall not be reproduced wholly or in part, nor disclosed to others without specific written permission.

HARDWARE NAME:EVAL-RHP50000-CSLZ


HARDWARE NUMBER:BR-100211

ENGINEER:J. GONZALES

DESIGNER:M. VALE

DATE: 07/4/2025

ODB++/GERBER:PASTE_TOP





This document contains information considered proprietary, and shall not be reproduced wholly or in part, nor disclosed to others without specific written permission.

HARDWARE NAME:EVAL-RHP50000-CSLZ

HARDWARE NUMBER:BR-100211

ENGINEER:J. GONZALES

DESIGNER:M. VALE

DATE: 07/4/2025

ODB++/GERBER:PASTE_BOT

