

D

C

B

A

D

C

B

A

maxim
integrated™

HARDWARE NAME:

MAX17523A_EVKIT_A

HARDWARE NUMBER:

XX-XXXX-XXX

NOT TO SCALE

TEMPLATE REV:

SHEET 1 OF 1

REV

A

maxim
integrated™

HARDWARE NAME:

MAX17523A_EVKIT_A

HARDWARE NUMBER:

XX-XXXX-XXX

NOT TO SCALE

TEMPLATE REV:

SHEET 1 OF 1

REV

A

maxim
integrated™

HARDWARE NAME:

MAX17523A_EVKIT_A

HARDWARE NUMBER:

XX-XXXX-XXX

NOT TO SCALE

TEMPLATE REV:

SHEET 1 OF 1

REV

A

PCB layout diagram showing dimensions 2.70 and 2.20, and a scale bar.

LAMINATION DIAGRAM				
LAYER NUMBER	LAYER NAME	COPPER THICKNESS (OZ./INCH)	DIELECTRIC THICKNESS (INCH)	MATERIALS
1	TOP	1 OZ. 0.0014" MIN.		FINAL CU (THICKNESS AFTER PLATING)
			TBD	ISOLA 370HR/EQUIVALENT
2	BOTTOM	1 OZ. 0.0014" MIN.		FINAL CU (THICKNESS AFTER PLATING)
THE FINISHED PCB THICKNESS TO BE: 0.0625" +/- 0.010"				

DRILL CHART: TOP to BOTTOM				
ALL UNITS ARE IN MILS				
FIGURE	SIZE	TOLERANCE	PLATED	QTY
△	10.0	+3.0/-8.0	PLATED	4
△	18.0	+3.0/-16.0	PLATED	28
⊙	29.53	+3.0/-3.0	PLATED	3
⊙	35.43	+3.0/-3.0	PLATED	4
⊙	37.4	+3.0/-3.0	PLATED	4
⊙	39.37	+3.0/-3.0	PLATED	11
⊙	45.28	+3.0/-3.0	PLATED	8
⊙	47.24	+3.0/-3.0	PLATED	24
⊙	51.18	+3.0/-3.0	PLATED	4
⊙	90.55	+3.0/-3.0	PLATED	2
⊙	125.0	+3.0/-3.0	PLATED	4

NOTES:

- UNLESS OTHERWISE SPECIFIED
- DIMENSIONS ARE IN INCHES (EXCEPT WHERE NOTED).
- MATERIAL: (USE CHECKED ITEMS FOR MATERIAL)
- BOARD MATERIAL:
 - (X) ISOLA 370HR OR EQUIVALENT
 - () ISOLA-FR408HR OR EQUIVALENT
 - () NELCO-4000-13
 - () MEGTRON 6
 - () ROGERS 4350B
 - () ROGERS 4003C
 - () OTHER _____
- THE PCB SHALL BE FABRICATED TO IPC-6012, TYPE X, CLASS 2.
- WORKMANSHIP SHALL CONFORM TO IPC-A-600, CLASS 2, CURRENT REVISIONS.
- BOARD MATERIAL & CONSTRUCTION SHALL MEET THE REQUIREMENTS OF UL796 WITH FLAMMABILITY RATING OF 94V-0.
- OVERALL BOARD THICKNESS REFER TO LAMINATION DIAGRAM. TOLERANCE APPLIES AFTER ALL LAMINATION AND PLATING PROCESSES. IT IS TO BE MEASURED FROM TOP PCB METAL TO BOTTOM PCB METAL UNLESS OTHERWISE SPECIFIED.
- BOW & TWIST NOT TO EXCEED 0.0075 IN. (0.75%) PER LINEAR INCH. BOW & TWIST SHOULD BE MEASURED PER IPC-TM-650, METHOD 2.4.22.

TOOLING:

- PHOTO ETCH CIRCUITRY PER ENCLOSED GERBER RS274X OR ODB++ FORMAT FILE. DRILL LOCATION AND SIZE CONTROLLED BY EXCELLOD CNC DRILL FILE.
- IMPEDANCE REQUIREMENTS: IF NO STACKUP IS DEFINED, THE VENDOR IS ALLOWED TO ADJUST THE DIELECTRIC THICKNESS AND TRACE WIDTHS TO MEET THE IMPEDANCE REQUIREMENT. IF SPECIFIED, VENDOR MUST FOLLOW AND MEET THE REQUIREMENTS LISTED IN THE IMPEDANCE TABLE. ANY ADJUSTMENTS MADE TO THE DEFINED STACKUP, TRACE WIDTH & SPACING THAT IMPACT THE REQUIREMENTS MUST HAVE WRITTEN APPROVAL FROM MAXIM.
- ALL TRACES FILLETED OPTION TO ENHANCE RELIABILITY AT PAD JUNCTIONS WHERE SPACING PERMITS, UNLESS OTHERWISE SPECIFIED:
 - () FILLETED
 - (X) NOT FILLETED
- LAYER TO LAYER REGISTRATIONS SHALL BE WITHIN .003 INCHES. LEGEND TO LEGEND +/- 0.007 INCHES
- FINISHED COPPER WEIGHT/THICKNESS:
 - (X) REFER TO LAMINATION DIAGRAM FOR FINISHED COPPER WEIGHT/THICKNESS REQUIREMENTS. THE STARTING COPPER WEIGHT/THICKNESS CAN VARY AS LONG AS THE FINISHED COPPER WEIGHT/THICKNESS IS NOT LESS THAN THE SPECIFIED VALUE, UNLESS OTHERWISE SPECIFIED.
 - () OTHER _____

SURFACE FINISH:

- USE CHECKED ITEMS FOR PLATING
 - () ELECTRODEPOSITED HARD GOLD PLATE, TYPE 1 (99.7% MIN GOLD), GRADE C (KNOOP HARDNESS 130-200), CLASS 1 (50-100 MICRO INCHES THICK) IN ACCORDANCE WITH MIL-G-45204C. GENERAL SURFACING REQUIREMENTS MUST MEET ANSI/IPC-A-600(CURRENT REV) SECTION 4.0, CLASS 3 (50-100 MICROINCHES THICK) OVER ELECTRODEPOSITED NICKEL PLATE IN ACCORDANCE WITH ANSI/IPC-A-600D, SECTION 4.0, CLASS 3 (200-400 MICROINCHES THICK).
 - (X) FINISH CONDUCTOR SURFACES: IMMERSION GOLD, 1.58-3.94 MICRO INCHES OVER 118-236 MICRO INCHES MINIMUM OF ELECTROLESS NICKEL.
 - () FINGERS TO BE GOLD PLATED.
 - () OTHER _____
- DRILL SIZES ARE FINISHED HOLE SIZES. ALL HOLES SHALL BE LOCATED WITHIN .005 DTP, UNLESS SPECIFIED. MINIMUM BARREL PLATING OF .001 IN. PLATED HOLES SHALL NOT BE ROUGH OR IRREGULAR SO AS TO HINDER PROPER SOLDER WICKING. BARREL RELIEF ON SOLDERMASK ALLOWED ON UNFILLED VIA IN PAD HOLES. SOLDERMASK:
- SOLDERMASK OVER BARE COPPER OR BARE GOLD (BOTH SIDES) WITH LIQUID PHOTO IMAGEABLE (LPI) INK IF PRESENT, DO NOT MODIFY SOLDERMASK DEFINED PADS (MASK OPENINGS LESS THAN COPPER PAD) WITHOUT APPROVAL.
 - () CUSTOM MAXIM TEAL SOLDER MASK, PANTONE #326C.
 - (X) OTHER _____GREEN_____

SILKSCREEN:

- APPLY SILKSCREEN USING A NON-CONDUCTIVE EPOXY INK
 - (X) WHITE
 - () OTHER _____
- VENDOR LOGO & DATE CODE REQUIREMENT. DATE CODE FORMAT MUST BE YYWW ONLY
 - (X) PLACE ON BOTTOM LEGEND LAYER. IF NO BOTTOM LEGEND SUPPLIED, CREATE BOTTOM LEGEND LAYER TO ADD.
 - () PLACE ON TOP LEGEND LAYER. IF NO TOP LEGEND SUPPLIED, CREATE TOP LEGEND LAYER TO ADD.
 - () OTHER _____

TESTING:

- FINAL ELECTRICAL TEST TO BE PERFORMED USING PROVIDED IPC-D-356A NETLIST OR ODB++ FORMAT FILE. (REQUIRED UNLESS OTHERWISE SPECIFIED IN QUOTE)
THE PCB SHALL HAVE A VERIFICATION STAMP.
- A TIME DOMAIN REFLECTOMETER REPORT FOR EACH IMPEDANCE CONTROLLED LAYER AND A CERTIFICATE OF COMPLIANCE SHALL BE PROVIDED BY VENDOR AT TIME OF SHIPMENT. INSTANCES WHERE TOR TESTING CAN'T BE PERFORMED BECAUSE THE TRACE LENGTH IS TOO SHORT ON THE OUTER LAYERS AT THE PIN ESCAPES IS ACCEPTABLE. ALL OTHER INSTANCES MUST BE REPORTED.

MISCELLANEOUS:

- IF PRESENT, ALL BLIND/BURIED VIAS WITH AN ASPECT RATIO <1:1 TO BE PLATED SHUT WITH COPPER WHEN USED AS VIA-IN PAD OR AS A STACKED VIA. BLIND/BURIED VIAS WITH AN ASPECT RATIO >1:1 TO BE FILLED WITH NON-CONDUCTIVE EPOXY, UNLESS OTHERWISE SPECIFIED.
- FOR ALL DRILL INFORMATION REFER TO DRILL CHART.
 - () NON-CONDUCTIVE EPOXY, FILL AND CAP ALL 0.000X INCH DRILLED VIAS.
 - () SILVER, FILL AND CAP ALL 0.000X INCH DRILLED VIAS.
- FINISHED SURFACE CONTACTS AND FILLED VIAS TO BE FREE OF ANY PITS, SCRATCHES, PROBE MARKS OR OTHER DEFORMITIES THAT COULD EFFECT THE APPEARANCE AND PERFORMANCE OF THE CONTACT SURFACE. CONTACTS ARE TO BE AS FLAT AS POSSIBLE. NOT TO EXCEED +/- 0.001" OF FLATNESS.
- THEFTING:
 - () SUPPLIER MAY ADD THEFTING TO COMPENSATE FOR LOW COPPER DENSITY AREAS ON THIS DESIGN.
 - (X) SUPPLIER MAY NOT ADD THEFTING TO COMPENSATE FOR LOW COPPER DENSITY AREAS ON THIS DESIGN.
- PENMUT
 - () PENMUTS TO BE INSTALLED BY FABRICATOR.
 - () PENMUTS NOT TO BE INSTALLED BY FABRICATOR.
 - (X) NOT APPLICABLE.