



This document contains information considered proprietary,
and shall not be reproduced wholly or in part,
nor disclosed to others without specific written permission.

HARDWARE NAME: MAX20457 Evaluation Kit


HARDWARE NUMBER: MAX20457EVKIT#

ENGINEER: JB

DESIGNER: JB

DATE: 07/12/2018

ODB++/GERBER: TOP





This document contains information considered proprietary, and shall not be reproduced wholly or in part, nor disclosed to others without specific written permission.

HARDWARE NAME: MAX20457 Evaluation Kit


HARDWARE NUMBER: MAX20457EVKIT#

ENGINEER: JB

DESIGNER: JB

DATE: 07/12/2018

ODB++/GERBER: INTERNAL2





This document contains information considered proprietary, and shall not be reproduced wholly or in part, nor disclosed to others without specific written permission.

HARDWARE NAME: MAX20457 Evaluation Kit


HARDWARE NUMBER: MAX20457EVKIT#

ENGINEER: JB

DESIGNER: JB

DATE: 07/12/2018

ODB++/GERBER: INTERNAL3





This document contains information considered proprietary, and shall not be reproduced wholly or in part, nor disclosed to others without specific written permission.

HARDWARE NAME: MAX20457 Evaluation Kit


HARDWARE NUMBER: MAX20457EVKIT#

ENGINEER: JB

DESIGNER: JB

DATE: 07/12/2018

ODB++/GERBER: BOTTOM




**maxim
integrated**

This document contains information considered proprietary,
and shall not be reproduced wholly or in part,
nor disclosed to others without specific written permission.

HARDWARE NAME: MAX20457 Evaluation Kit


HARDWARE NUMBER: MAX20457EVKIT#

ENGINEER: JB

DESIGNER: JB

DATE: 07/12/2018

ODB++/GERBER: SILK_TOP



maxim
integrated™

This document contains information considered proprietary, and shall not be reproduced wholly or in part, nor disclosed to others without specific written permission.

HARDWARE NAME: MAX20457 Evaluation Kit


HARDWARE NUMBER: MAX20457EVKIT#

ENGINEER: JB

DESIGNER: JB

DATE: 07/12/2018

ODB++/GERBER: SILK_BOT



**maxim
integrated**

This document contains information considered proprietary,
and shall not be reproduced wholly or in part,
nor disclosed to others without specific written permission.

HARDWARE NAME: MAX20457 Evaluation Kit


HARDWARE NUMBER: MAX20457EVKIT#

ENGINEER: JB

DESIGNER: JB

DATE: 07/12/2018

ODB++/GERBER: MASK_TOP





This document contains information considered proprietary, and shall not be reproduced wholly or in part, nor disclosed to others without specific written permission.

HARDWARE NAME: MAX20457 Evaluation Kit


HARDWARE NUMBER: MAX20457EVKIT#

ENGINEER: JB

DESIGNER: JB

DATE: 07/12/2018

ODB++/GERBER: MASK_BOT



REVISIONS			
REV	DESCRIPTION	APPROVED	DATE
A	RELEASE		

- NOTES:
- UNLESS OTHERWISE SPECIFIED
1. DIMENSIONS ARE IN INCHES (EXCEPT WHERE NOTED).
- MATERIAL: (USE CHECKED ITEMS FOR MATERIAL)
2. BOARD MATERIAL:
- (X) FR4 (RoHS COMPLIANT) OR EQUIVALENT
- () ISOLA-FR408HR
- () NELCO-4000-13 OR EQUIVALENT
- () 370HR (RoHS COMPLIANT) OR EQUIVALENT
- () ROGERS 4350B/FR408HR
- () ROGERS 4003C/FR408HR
- () OTHER _____
3. THE PCB SHALL BE FABRICATED TO IPC-6012, TYPE X, CLASS 2.
- WORKMANSHIP SHALL CONFORM TO IPC-A-600, CLASS 2, CURRENT REVISIONS.
4. BOARD MATERIAL & CONSTRUCTION SHALL MEET THE REQUIREMENTS OF UL796 WITH FLAMMABILITY RATING OF 94V-0.
5. OVERALL BOARD THICKNESS REFER TO LAMINATION DIAGRAM. TOLERANCE APPLIES AFTER ALL LAMINATION AND PLATING PROCESSES. IT IS TO BE MEASURED FROM TOP PCB METAL TO BOTTOM PCB METAL UNLESS OTHERWISE SPECIFIED.
6. BOW & TWIST NOT TO EXCEED 0.0015 IN. (0.75%) PER LINEAR INCH. BOW & TWIST SHOULD BE MEASURED PER IPC-TM-650, METHOD 2.4.22.
- TOOLING: (USE CHECKED ITEMS FOR TOOLING)
7. PHOTO ETCH CIRCUITRY PER ENCLOSED GERBER RS274X OR ODB++ FORMAT FILE. DRILL LOCATION AND SIZE CONTROLLED BY EXCELLON CNC DRILL FILE.
8. IF STATED IN THE LAMINATION DIAGRAM, THE DIELECTRIC THICKNESS OF ANY CONTROLLED IMPEDANCE LAYER IS FOR REFERENCE ONLY. FINAL ACCEPTANCE SHALL BE DETERMINED BY THESE LAYERS HAVING A CHARACTERISTIC IMPEDANCE OF +/-10% OHMS AS STATED IN THE LAMINATION DIAGRAM. THE VENDOR CAN MAKE ADJUSTMENTS AS LONG AS THE STATED IMPEDANCE AND OVERALL BOARD THICKNESS IS MAINTAINED. ANY ADJUSTMENT MADE TO TRACE WIDTH OR SPACING MUST HAVE PRIOR WRITTEN APPROVAL FROM MAXIM.
9. ALL TRACES FILLETED OPTION TO ENHANCE RELIABILITY AT PAD JUNCTIONS WHERE SPACING PERMITS. UNLESS OTHERWISE SPECIFIED:
- () FILLETED
- (X) NOT FILLETED
10. LAYER TO LAYER REGISTRATIONS SHALL BE WITHIN .003 INCHES. LEGEND TO LEGEND +/- 0.007 INCHES
- FINISH: (USE CHECKED ITEMS FOR PLATING)
11. PLATING SPECIFICATION:
- () STARTING AND FINISH COPPER WEIGHT FOR OUTER LAYERS TO BE (1 OZ). FOR OUTER LAYERS WHERE SPACING PREVENTS THE USE OF (1 OZ) AS A STARTING WEIGHT, THE STARTING WEIGHT CAN BE (0.5 OZ) AS LONG AS THE FINISH COPPER WEIGHT IS (1 OZ) UNLESS OTHERWISE SPECIFIED
- (X) STARTING COPPER WEIGHT FOR OUTER LAYERS TO BE (1 OZ), THE FINISH COPPER WEIGHT IS (2 OZ). FOR OUTER LAYERS WHERE SPACING PREVENTS THE USE OF (1 OZ) AS A STARTING WEIGHT, THE STARTING WEIGHT CAN BE (0.5 OZ) AS LONG AS THE FINISH COPPER WEIGHT IS (2 OZ). UNLESS OTHERWISE SPECIFIED
- () STARTING COPPER WEIGHT FOR OUTER LAYERS TO BE (2 OZ), THE FINISH COPPER WEIGHT IS (2 OZ)MINIMUM. FOR OUTER LAYERS WHERE SPACING PREVENTS THE USE OF (1 OZ) AS A STARTING WEIGHT, THE STARTING WEIGHT CAN BE (1/2 OZ) AS LONG AS THE FINISH COPPER WEIGHT IS (2 OZ). UNLESS OTHERWISE SPECIFIED
- () OTHER _____
12. CHECK ALL THAT APPLY
- () FINISH CONDUCTOR SURFACES: IMMERSION GOLD, 3-8 MICRO INCHES OVER 100 MICRO INCHES MINIMUM OF ELECTROLESS NICKEL.
- (X) LEAD FREE AND RoHS COMPLIANT OR EQUIVALENT LEAD-FREE PLATING
- () ELECTRODEPOSITED HARD GOLD PLATE, TYPE 1 (99.7% MIN GOLD), GRADE C (KNOOP HARDNESS 130-200), CLASS 1 (50-100 MICRO INCHES THICK) IN ACCORDANCE WITH MIL-G-45204C. GENERAL SURFACING REQUIREMENTS MUST MEET ANSI/IPC-A-600(CURRENT REV) SECTION 4.0. CLASS 3 (50-100 MICROINCHES THICK) OVER ELECTRODEPOSITED NICKEL PLATE IN ACCORDANCE WITH ANSI/IPC-A-600D, SECTION 4.0, CLASS 3 (200-600 MICROINCHES THICK).
- () FINISH CONDUCTOR SURFACES: IMMERSION GOLD, 2-5 MICRO INCHES OVER 118-236 MICRO INCHES MINIMUM OF ELECTROLESS NICKEL.
- () FINGERS TO BE GOLD PLATED.
- () OTHER _____
13. DRILL SIZES ARE FINISHED HOLE SIZES. ALL HOLES SHALL BE LOCATED WITHIN .005 DTP. MINIMUM BARREL PLATING OF .001 IN. PLATED HOLES SHALL NOT BE ROUGH OR IRREGULAR SO AS TO HINDER PROPER SOLDER WICKING.
14. CHECK ALL THAT APPLY
- () GREEN SOLDERMASK OVER BARE COPPER/BARE GOLD (BOTH SIDES) WITH LIQUID PHOTO IMAGEABLE (LPI) PER ARTWORK.
- () GREEN TAIYO PSR-4000
15. CHECK ALL THAT APPLY
- () APPLY SILKSCREEN TO BOTH SIDES USING A NON-CONDUCTIVE, WHITE EPOXY BASED INK PER ARTWORK.
- () APPLY SILKSCREEN TO TOP SIDE USING A NON-CONDUCTIVE, WHITE EPOXY BASED INK PER ARTWORK.
- () OTHER _____
16. VENDOR LOGO & DATE CODE REQUIRED IN LEGEND ON BOTTOM SIDE ONLY. DATE CODE FORMAT MUST BE YYYY ONLY IF NO BOTTOM LEGEND SUPPLIED. VENDOR CAN CREATE BOTTOM LEGEND LAYER TO ADD LOGO & DATE CODE.
- TESTING:
17. FINAL ELECTRICAL TEST TO BE PERFORMED USING PROVIDED IPC-D-356A NETLIST OR ODB++ FORMAT FILE. (REQUIRED UNLESS OTHERWISE SPECIFIED IN QUOTE) THE PCB SHALL HAVE A VERIFICATION STAMP.
18. A TIME DOMAIN REFLECTOMETER REPORT FOR EACH IMPEDANCE CONTROLLED LAYER AND A CERTIFICATE OF COMPLIANCE SHALL BE PROVIDED BY VENDOR AT TIME OF SHIPMENT.
- MISCELLANEOUS:
19. FOR BLIND AND BURIED VIA INFORMATION REFER TO DRILL CHART.
- () NON-CONDUCTIVE EPOXY FILL AND CAP ALL 0.1XXX INCH DRILLED VIAS.
- () SILVER FILL AND CAP ALL 0.1XXX INCH DRILLED VIAS.
21. ALL MICRO-VIAS LESS THAN 0.006 INCHES FHS WILL BE PLATED SHUT WITH COPPER, UNLESS OTHERWISE SPECIFIED.
22. FOR VIA SIZES XX.XX INCH USE NON CONDUCTIVE VIA FILL AND CAP
23. FINISHED SURFACE CONTACTS AND FILLED VIAS TO BE FREE OF ANY PITS, SCRATCHES, PROBE MARKS OR OTHER DEFORMITIES THAT COULD EFFECT THE APPEARANCE AND PERFORMANCE OF THE CONTACT SURFACE. CONTACTS ARE TO BE AS FLAT AS POSSIBLE. NOT TO EXCEED +/- 0.001" OF FLATNESS.
24. THEIVING:
- (X) SUPPLIER MAY ADD THEIVING TO COMPENSATE FOR LOW COPPER DENSITY AREAS ON THIS DESIGN.
- () SUPPLIER MAY NOT ADD THEIVING TO COMPENSATE FOR LOW COPPER DENSITY AREAS ON THIS DESIGN.
25. PENMUT
- () PENMUT TO BE INSTALLED BY SUPPLIER
- () PENMUT NOT TO BE INSTALLED BY SUPPLIER

maxim
integrated™

© 2014 Maxim Integrated Products, Inc.
All rights reserved. No part of this document may be reproduced without written permission from Maxim Integrated Products, Inc.

WORKING NAME: MAXIMIST EVALUATOR KIT

WORKING NUMBER: MAXIMISTEVALKIT

ENGINEER: JB DESIGNER: JB

DATE: 07/10/2018 ODB++/GERBER: FAB NOTES

