

LINEAR TECHNOLOGY MATERIALS DECLARATION

1t6108ims8-1#trpbf				(Engineering Calculation)		MSOP
(printed on: 2020-07-11 20:39:27)					TOTAL MASS (g) : 0.026483	
COMPONENT MATERIAL	VENDOR/ INDUSTRY NAMES	CONSTITUENT NAME	CAS NUMBER	CONSTITUENT MASS (g)	CONSTITUENT (PPM) OF MATERIAL	CONSTITUENT (PPM) OF TOTAL PKG.
Active Device	Linear Technology	Silicon (Si)	7440-21-3	0.001409	1000000	53203.890625
Die Coat	Dow Corning	Silicone	69430-27-9	0.000000	0	0
Lead Frame	Cu	Copper (Cu)	7440-50-8	0.010433	975000	393950.4375
		Iron (Fe)	7439-89-6	0.000257	24000	9704.33007812
		Phosphorus (P)	7723-14-0	0.000003	300	113.28011322
		Zinc (Zn)	7440-66-6	0.000007	700	264.320251465
		Nickel (Ni)	7440-02-0	0.000000	0	0
		Silicon (Si)	7440-21-3	0.000000	0	0
		Magnesium (Mg)	7439-95-4	0.000000	0	0
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead Frame Total:		0.010700	1000000	404032.40625
Plating	PMI	Exter. Plating Pb	7439-92-1	0.000000	0	0
		Exter. Plating Sn	7440-31-5	0.000710	1000000	26810.5683594
		External Plating Total:		0.000710	1000000	26810.5683594
		Inter. Plating Ni	7440-02-0	0.000000	0	0
		Inter. Plating Ag	7440-22-4	0.000086	1000000	3247.36303711
		Internal Plating Total:		0.000086	1000000	3247.36303711
Die Attach	ELECTRICALLY CONDUCTIVE ADHESIVE	Silver (Ag)	7440-22-4	0.000546	750000	20616.9804688
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead (Pb)	7439-92-1	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.000000	0	0
		Indium (In)	7440-74-6	0.000000	0	0
		Metal Oxide		0.000000	0	0
		Antimony (Sb)	7440-36-0	0.000000	0	0
		Resin (EP)		0.000182	250000	6872.32666016
		Die Attach Total:		0.000728	1000000	27489.3066406
Encapsulation	MULTI-AROMATIC RESIN Br/Sb FREE	Resin (EP)		0.001659	130000	62643.9023438
		Bromine (Br)	40039-93-8	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.010591	830000	399916.5625
		Antimony Trioxide (Sb2O3)	1309-64-4	0.000000	0	0
		Metal Hydroxide		0.000447	35000	16878.734375
		Carbon Black (C)	1333-86-4	0.000064	5000	2416.64233398
		Encapsulation Total:		0.012761	1000000	481855.8125
Bond Wire Estimated	AFW/TANAKA/ Kn	Gold (Au)	7440-57-5	0.000089	1000000	3360.64331055
					TOTAL MASS (g) :	0.026483