

LINEAR TECHNOLOGY MATERIALS DECLARATION

1t1498cs8#pbf

(Engineering Calculation)

SOIC

(printed on: 2020-07-11 19:08:53)

TOTAL MASS (g) : 0.076308

| COMPONENT MATERIAL | VENDOR/ INDUSTRY NAMES | CONSTITUENT NAME | CAS NUMBER | CONSTITUENT MASS (g) | CONSTITUENT (PPM) OF MATERIAL | CONSTITUENT (PPM) OF TOTAL PKG. | | |
|--------------------------------|----------------------------------|--------------------------------|------------|----------------------|-------------------------------|---------------------------------|----------------|----------------------|
| Active Device | Linear Technology | Silicon (Si) | 7440-21-3 | 0.004397 | 1000000 | 57621.859375 | | |
| Die Coat | Dow Corning | Silicone | 69430-27-9 | 0.000183 | 1000000 | 2398.18066406 | | |
| Lead Frame | A42 | Copper (Cu) | 7440-50-8 | 0.000000 | 0 | 0 | | |
| | | Iron (Fe) | 7439-89-6 | 0.014071 | 580000 | 184397.796875 | | |
| | | Phosphorus (P) | 7723-14-0 | 0.000000 | 0 | 0 | | |
| | | Zinc (Zn) | 7440-66-6 | 0.000000 | 0 | 0 | | |
| | | Nickel (Ni) | 7440-02-0 | 0.010189 | 420000 | 133524.921875 | | |
| | | Silicon (Si) | 7440-21-3 | 0.000000 | 0 | 0 | | |
| | | Magnesium (Mg) | 7439-95-4 | 0.000000 | 0 | 0 | | |
| | | Tin (Sn) | 7440-31-5 | 0.000000 | 0 | 0 | | |
| Lead Frame Total: | | | | 0.024260 | 1000000 | 317922.75 | | |
| Plating | PMI | Exter. Plating Pb | 7439-92-1 | 0.000000 | 0 | 0 | | |
| | | Exter. Plating Sn | 7440-31-5 | 0.001477 | 1000000 | 19353.8691406 | | |
| | | External Plating Total: | | | | 0.001477 | 1000000 | 19353.8691406 |
| | | Inter. Plating Ni | 7440-02-0 | 0.000000 | 0 | 0 | | |
| | | Inter. Plating Ag | 7440-22-4 | 0.000194 | 1000000 | 2542.33349609 | | |
| Internal Plating Total: | | | | 0.000194 | 1000000 | 2542.33349609 | | |
| Die Attach | ELECTRICALLY CONDUCTIVE ADHESIVE | Silver (Ag) | 7440-22-4 | 0.001189 | 750000 | 15581.6210938 | | |
| | | Tin (Sn) | 7440-31-5 | 0.000000 | 0 | 0 | | |
| | | Lead (Pb) | 7439-92-1 | 0.000000 | 0 | 0 | | |
| | | Silica (SiO2) | 60676-86-0 | 0.000000 | 0 | 0 | | |
| | | Indium (In) | 7440-74-6 | 0.000000 | 0 | 0 | | |
| | | Metal Oxide | | 0.000000 | 0 | 0 | | |
| | | Antimony (Sb) | 7440-36-0 | 0.000000 | 0 | 0 | | |
| | | Resin (EP) | | 0.000396 | 250000 | 5189.50537109 | | |
| Die Attach Total: | | | | 0.001585 | 1000000 | 20771.1269531 | | |
| Encapsulation | MULTI-AROMATIC RESIN Br/Sb FREE | Resin (EP) | | 0.006604 | 150000 | 86544.1796875 | | |
| | | Bromine (Br) | 40039-93-8 | 0.000000 | 0 | 0 | | |
| | | Silica (SiO2) | 60676-86-0 | 0.036102 | 820000 | 473109.9375 | | |
| | | Antimony Trioxide (Sb2O3) | 1309-64-4 | 0.000000 | 0 | 0 | | |
| | | Metal Hydroxide | | 0.001101 | 25000 | 14428.3974609 | | |
| | | Carbon Black (C) | 1333-86-4 | 0.000220 | 5000 | 2883.05883789 | | |
| | | Encapsulation Total: | | | | 0.044027 | 1000000 | 576965.5625 |
| Bond Wire Estimated | AFW/TANAKA/ Kn | Gold (Au) | 7440-57-5 | 0.000185 | 1000000 | 2424.39038086 | | |
| | | | | | TOTAL MASS (g) : | 0.076308 | | |