

LINEAR TECHNOLOGY MATERIALS DECLARATION

ltc2055hms8#pbf

(Engineering Calculation)

MSOP

(printed on: 2020-07-11 18:18:44)

TOTAL MASS (g) : 0.027168

COMPONENT MATERIAL	VENDOR/ INDUSTRY NAMES	CONSTITUENT NAME	CAS NUMBER	CONSTITUENT MASS (g)	CONSTITUENT (PPM) OF MATERIAL	CONSTITUENT (PPM) OF TOTAL PKG.
Active Device	Linear Technology	Silicon (Si)	7440-21-3	0.001929	1000000	71002.578125
Die Coat	Dow Corning	Silicone	69430-27-9	0.000000	0	0
Lead Frame	Cu	Copper (Cu)	7440-50-8	0.010433	975000	384017.59375
		Iron (Fe)	7439-89-6	0.000257	24000	9459.64941406
		Phosphorus (P)	7723-14-0	0.000003	300	110.423927307
		Zinc (Zn)	7440-66-6	0.000007	700	257.655822754
		Nickel (Ni)	7440-02-0	0.000000	0	0
		Silicon (Si)	7440-21-3	0.000000	0	0
		Magnesium (Mg)	7439-95-4	0.000000	0	0
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead Frame Total:		0.010700	1000000	393845.34375
Plating	PMI	Exter. Plating Pb	7439-92-1	0.000000	0	0
		Exter. Plating Sn	7440-31-5	0.000710	1000000	26134.5800781
		External Plating Total:		0.000710	1000000	26134.5800781
		Inter. Plating Ni	7440-02-0	0.000000	0	0
		Inter. Plating Ag	7440-22-4	0.000086	1000000	3165.48583984
		Internal Plating Total:		0.000086	1000000	3165.48583984
Die Attach	ELECTRICALLY CONDUCTIVE ADHESIVE	Silver (Ag)	7440-22-4	0.000670	750000	24661.3417969
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead (Pb)	7439-92-1	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.000000	0	0
		Indium (In)	7440-74-6	0.000000	0	0
		Metal Oxide		0.000000	0	0
		Antimony (Sb)	7440-36-0	0.000000	0	0
		Resin (EP)		0.000223	250000	8208.17773438
		Die Attach Total:		0.000893	1000000	32869.5234375
Encapsulation	MULTI-AROMATIC RESIN Br/Sb FREE	Resin (EP)		0.001659	130000	61064.4257812
		Bromine (Br)	40039-93-8	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.010591	830000	389833.28125
		Antimony Trioxide (Sb2O3)	1309-64-4	0.000000	0	0
		Metal Hydroxide		0.000447	35000	16453.1640625
		Carbon Black (C)	1333-86-4	0.000064	5000	2355.71044922
		Encapsulation Total:		0.012761	1000000	469706.53125
Bond Wire Estimated	AFW/TANAKA/ Kn	Gold (Au)	7440-57-5	0.000089	1000000	3275.90966797
					TOTAL MASS (g) :	0.027168