

LINEAR TECHNOLOGY MATERIALS DECLARATION

1t6200cs6#trpbf

(Engineering Calculation)

TSOT-23

(printed on: 2020-07-11 20:39:37)

TOTAL MASS (g) : 0.012599

COMPONENT MATERIAL	VENDOR/ INDUSTRY NAMES	CONSTITUENT NAME	CAS NUMBER	CONSTITUENT MASS (g)	CONSTITUENT (PPM) OF MATERIAL	CONSTITUENT (PPM) OF TOTAL PKG.
Active Device	Linear Technology	Silicon (Si)	7440-21-3	0.000575	1000000	45639.4257812
Die Coat	Dow Corning	Silicone	69430-27-9	0.000000	0	0
Lead Frame	Cu	Copper (Cu)	7440-50-8	0.004582	975000	363686.6875
		Iron (Fe)	7439-89-6	0.000113	24000	8969.13964844
		Phosphorus (P)	7723-14-0	0.000001	300	79.3729095459
		Zinc (Zn)	7440-66-6	0.000003	700	238.118743896
		Nickel (Ni)	7440-02-0	0.000000	0	0
		Silicon (Si)	7440-21-3	0.000000	0	0
		Magnesium (Mg)	7439-95-4	0.000000	0	0
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead Frame Total:		0.004699	1000000	372973.3125
Plating	PMI	Exter. Plating Pb	7439-92-1	0.000000	0	0
		Exter. Plating Sn	7440-31-5	0.000644	1000000	51096.7890625
		External Plating Total:		0.000644	1000000	51096.7890625
		Inter. Plating Ni	7440-02-0	0.000000	0	0
		Inter. Plating Ag	7440-22-4	0.000080	1000000	6349.83251953
		Internal Plating Total:		0.000080	1000000	6349.83251953
Die Attach	ELECTRICALLY CONDUCTIVE ADHESIVE	Silver (Ag)	7440-22-4	0.000411	750000	32622.265625
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead (Pb)	7439-92-1	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.000000	0	0
		Indium (In)	7440-74-6	0.000000	0	0
		Metal Oxide		0.000000	0	0
		Antimony (Sb)	7440-36-0	0.000000	0	0
		Resin (EP)		0.000137	250000	10874.0888672
		Die Attach Total:		0.000548	1000000	43496.3554688
Encapsulation	MULTI-AROMATIC RESIN Br/Sb FREE	Resin (EP)		0.000772	130000	61275.8867188
		Bromine (Br)	40039-93-8	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.004930	830000	391308.4375
		Antimony Trioxide (Sb2O3)	1309-64-4	0.000000	0	0
		Metal Hydroxide		0.000208	35000	16509.5644531
		Carbon Black (C)	1333-86-4	0.000030	5000	2381.1875
		Encapsulation Total:		0.005940	1000000	471475.09375
Bond Wire Estimated	AFW/TANAKA/ Kn	Gold (Au)	7440-57-5	0.000113	1000000	8969.13964844
					TOTAL MASS (g) :	0.012599