

LINEAR TECHNOLOGY MATERIALS DECLARATION

1t6550ims#trpbf		(Engineering Calculation)				MSOP
(printed on: 2020-07-11 20:40:47)					TOTAL MASS (g) : 0.026871	
COMPONENT MATERIAL	VENDOR/ INDUSTRY NAMES	CONSTITUENT NAME	CAS NUMBER	CONSTITUENT MASS (g)	CONSTITUENT (PPM) OF MATERIAL	CONSTITUENT (PPM) OF TOTAL PKG.
Active Device	Linear Technology	Silicon (Si)	7440-21-3	0.001650	1000000	61404.4296875
Die Coat	Dow Corning	Silicone	69430-27-9	0.000000	0	0
Lead Frame	Cu	Copper (Cu)	7440-50-8	0.010433	975000	388262.0625
		Iron (Fe)	7439-89-6	0.000257	24000	9564.20507812
		Phosphorus (P)	7723-14-0	0.000003	300	111.644416809
		Zinc (Zn)	7440-66-6	0.000007	700	260.503631592
		Nickel (Ni)	7440-02-0	0.000000	0	0
		Silicon (Si)	7440-21-3	0.000000	0	0
		Magnesium (Mg)	7439-95-4	0.000000	0	0
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead Frame Total:		0.010700	1000000	398198.4375
Plating	PMI	Exter. Plating Pb	7439-92-1	0.000000	0	0
		Exter. Plating Sn	7440-31-5	0.000710	1000000	26423.4414062
		External Plating Total:		0.000710	1000000	26423.4414062
		Inter. Plating Ni	7440-02-0	0.000000	0	0
		Inter. Plating Ag	7440-22-4	0.000086	1000000	3200.47314453
		Internal Plating Total:		0.000086	1000000	3200.47314453
Die Attach	ELECTRICALLY CONDUCTIVE ADHESIVE	Silver (Ag)	7440-22-4	0.000639	750000	23780.2597656
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead (Pb)	7439-92-1	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.000000	0	0
		Indium (In)	7440-74-6	0.000000	0	0
		Metal Oxide		0.000000	0	0
		Antimony (Sb)	7440-36-0	0.000000	0	0
		Resin (EP)		0.000213	250000	7926.75390625
		Die Attach Total:		0.000852	1000000	31707.015625
Encapsulation	MULTI-AROMATIC RESIN Br/Sb FREE	Resin (EP)		0.001659	130000	61739.359375
		Bromine (Br)	40039-93-8	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.010591	830000	394142.03125
		Antimony Trioxide (Sb2O3)	1309-64-4	0.000000	0	0
		Metal Hydroxide		0.000447	35000	16635.0175781
		Carbon Black (C)	1333-86-4	0.000064	5000	2381.74755859
		Encapsulation Total:		0.012761	1000000	474898.125
Bond Wire Estimated	AFW/TANAKA/ Kn	Gold (Au)	7440-57-5	0.000112	1000000	4168.05810547
					TOTAL MASS (g) :	0.026871