

LINEAR TECHNOLOGY MATERIALS DECLARATION

ltc1542cdd#pbf

(Engineering Calculation)

DFN 3mm X 3mm Exp. Pad

(printed on: 2020-07-11 18:13:06)					TOTAL MASS (g) : 0.023029	
COMPONENT MATERIAL	VENDOR/ INDUSTRY NAMES	CONSTITUENT NAME	CAS NUMBER	CONSTITUENT MASS (g)	CONSTITUENT (PPM) OF MATERIAL	CONSTITUENT (PPM) OF TOTAL PKG.
Active Device	Linear Technology	Silicon (Si)	7440-21-3	0.001307	1000000	56753.6015625
Die Coat	Dow Corning	Silicone	69430-27-9	0.000000	0	0
Lead Frame	Cu	Copper (Cu)	7440-50-8	0.009350	975000	406003.1875
		Iron (Fe)	7439-89-6	0.000230	24000	9987.24414062
		Phosphorus (P)	7723-14-0	0.000003	300	130.268417358
		Zinc (Zn)	7440-66-6	0.000007	700	303.959625244
		Nickel (Ni)	7440-02-0	0.000000	0	0
		Silicon (Si)	7440-21-3	0.000000	0	0
		Magnesium (Mg)	7439-95-4	0.000000	0	0
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead Frame Total:		0.009590	1000000	416424.65625
Plating	PMI	Exter. Plating Pb	7439-92-1	0.000000	0	0
		Exter. Plating Sn	7440-31-5	0.000437	1000000	18992.0644531
		External Plating Total:		0.000437	1000000	18992.0644531
		Inter. Plating Ni	7440-02-0	0.000000	0	0
		Inter. Plating Ag	7440-22-4	0.000218	1000000	9466.16992188
		Internal Plating Total:		0.000218	1000000	9466.16992188
Die Attach	ELECTRICALLY CONDUCTIVE ADHESIVE	Silver (Ag)	7440-22-4	0.000677	750000	29397.234375
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead (Pb)	7439-92-1	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.000000	0	0
		Indium (In)	7440-74-6	0.000000	0	0
		Metal Oxide		0.000000	0	0
		Antimony (Sb)	7440-36-0	0.000000	0	0
		Resin (EP)		0.000226	250000	9813.55273438
		Die Attach Total:		0.000903	1000000	39210.7890625
Encapsulation	MULTI-AROMATIC RESIN Br/Sb FREE	Resin (EP)		0.001368	130000	59402.3945312
		Bromine (Br)	40039-93-8	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.009047	860000	392846.0625
		Antimony Trioxide (Sb2O3)	1309-64-4	0.000000	0	0
		Metal Hydroxide		0.000000	0	0
		Carbon Black (C)	1333-86-4	0.000105	10000	4559.39404297
		Encapsulation Total:		0.010520	1000000	456807.84375
Bond Wire Estimated	AFW/TANAKA/ Kn	Gold (Au)	7440-57-5	0.000054	1000000	2344.83129883
					TOTAL MASS (g) :	0.023029