

# LINEAR TECHNOLOGY MATERIALS DECLARATION

1tc1542cdd#trpbf

(Engineering Calculation)

DFN 3mm X 3mm Exp. Pad

(printed on: 2020-07-11 17:12:44)

**TOTAL MASS (g) : 0.023029**

| COMPONENT MATERIAL  | VENDOR/ INDUSTRY NAMES           | CONSTITUENT NAME          | CAS NUMBER | CONSTITUENT MASS (g) | CONSTITUENT (PPM) OF MATERIAL | CONSTITUENT (PPM) OF TOTAL PKG. |
|---------------------|----------------------------------|---------------------------|------------|----------------------|-------------------------------|---------------------------------|
| Active Device       | Linear Technology                | Silicon (Si)              | 7440-21-3  | 0.001307             | 1000000                       | 56753.6015625                   |
| Die Coat            | Dow Corning                      | Silicone                  | 69430-27-9 | 0.000000             | 0                             | 0                               |
| Lead Frame          | Cu                               | Copper (Cu)               | 7440-50-8  | 0.009350             | 975000                        | 406003.1875                     |
|                     |                                  | Iron (Fe)                 | 7439-89-6  | 0.000230             | 24000                         | 9987.24414062                   |
|                     |                                  | Phosphorus (P)            | 7723-14-0  | 0.000003             | 300                           | 130.268417358                   |
|                     |                                  | Zinc (Zn)                 | 7440-66-6  | 0.000007             | 700                           | 303.959625244                   |
|                     |                                  | Nickel (Ni)               | 7440-02-0  | 0.000000             | 0                             | 0                               |
|                     |                                  | Silicon (Si)              | 7440-21-3  | 0.000000             | 0                             | 0                               |
|                     |                                  | Magnesium (Mg)            | 7439-95-4  | 0.000000             | 0                             | 0                               |
|                     |                                  | Tin (Sn)                  | 7440-31-5  | 0.000000             | 0                             | 0                               |
|                     |                                  | Lead Frame Total:         |            | 0.009590             | 1000000                       | 416424.65625                    |
| Plating             | PMI                              | Exter. Plating Pb         | 7439-92-1  | 0.000000             | 0                             | 0                               |
|                     |                                  | Exter. Plating Sn         | 7440-31-5  | 0.000437             | 1000000                       | 18992.0644531                   |
|                     |                                  | External Plating Total:   |            | 0.000437             | 1000000                       | 18992.0644531                   |
|                     |                                  | Inter. Plating Ni         | 7440-02-0  | 0.000000             | 0                             | 0                               |
|                     |                                  | Inter. Plating Ag         | 7440-22-4  | 0.000218             | 1000000                       | 9466.16992188                   |
|                     |                                  | Internal Plating Total:   |            | 0.000218             | 1000000                       | 9466.16992188                   |
| Die Attach          | ELECTRICALLY CONDUCTIVE ADHESIVE | Silver (Ag)               | 7440-22-4  | 0.000677             | 750000                        | 29397.234375                    |
|                     |                                  | Tin (Sn)                  | 7440-31-5  | 0.000000             | 0                             | 0                               |
|                     |                                  | Lead (Pb)                 | 7439-92-1  | 0.000000             | 0                             | 0                               |
|                     |                                  | Silica (SiO2)             | 60676-86-0 | 0.000000             | 0                             | 0                               |
|                     |                                  | Indium (In)               | 7440-74-6  | 0.000000             | 0                             | 0                               |
|                     |                                  | Metal Oxide               |            | 0.000000             | 0                             | 0                               |
|                     |                                  | Antimony (Sb)             | 7440-36-0  | 0.000000             | 0                             | 0                               |
|                     |                                  | Resin (EP)                |            | 0.000226             | 250000                        | 9813.55273438                   |
|                     |                                  | Die Attach Total:         |            | 0.000903             | 1000000                       | 39210.7890625                   |
| Encapsulation       | MULTI-AROMATIC RESIN Br/Sb FREE  | Resin (EP)                |            | 0.001368             | 130000                        | 59402.3945312                   |
|                     |                                  | Bromine (Br)              | 40039-93-8 | 0.000000             | 0                             | 0                               |
|                     |                                  | Silica (SiO2)             | 60676-86-0 | 0.009047             | 860000                        | 392846.0625                     |
|                     |                                  | Antimony Trioxide (Sb2O3) | 1309-64-4  | 0.000000             | 0                             | 0                               |
|                     |                                  | Metal Hydroxide           |            | 0.000000             | 0                             | 0                               |
|                     |                                  | Carbon Black (C)          | 1333-86-4  | 0.000105             | 10000                         | 4559.39404297                   |
|                     |                                  | Encapsulation Total:      |            | 0.010520             | 1000000                       | 456807.84375                    |
| Bond Wire Estimated | AFW/TANAKA/ Kn                   | Gold (Au)                 | 7440-57-5  | 0.000054             | 1000000                       | 2344.83129883                   |
|                     |                                  |                           |            |                      | <b>TOTAL MASS (g) :</b>       | <b>0.023029</b>                 |