


POWER SOLUTIONS FOR PRECISION TECHNOLOGY SIGNAL CHAINS

ISOLATED GATE DRIVE & SENSE Multichannel Monitoring for Power Conversion with Digital Isolation Highest Voltage and Lowest Prop Delay

Rev. 0 | Jan. 2022



©2022 Analog Devices, Inc. All rights reserved.
Trademarks and registered trademarks are the
property of their respective owners.

This document is interactive. You can click on any underlined text to navigate through the document.

For the resources:

APPENDIX	<u>Parts Guide</u>
	<u>Power Requirements</u>

Left-click the Parts Guide and Power Requirements to go through the list of power devices and other references.

The Power Components are listed on the Appendix, and you may click on the part to go through its product page online.

PART #	DESCRIPTION
<u>LT3471</u>	Dual 1.3A, 1.2MHz Boost/Inverter in 3mm × 3mm DFN
<u>LT8604</u>	High Efficiency 42V/120mA Synchronous Buck
<u>LT8570-1</u>	Boost/SEPIC/Inverting DC/DC Converter with 65V Switch, Soft-Start and Sync.

For the individual pages:

Left-click the specific signal chain to go through its respective block diagram or power tree.

Non-isolated	POWER RE
<u>1-Channel</u>	
	PARAMETER
	Supply Voltage
	Supply Current
	PSRR

Isolated Gate Drive & Sense

Multichannel Monitoring for Power Conversion with Digital Isolation

Highest Voltage and Lowest Prop Delay

Isolated

Multichannel

PART #	DESCRIPTION
LT8604	High Efficiency 42V/120mA Synchronous Buck
LT3999	Low Noise, 1A, 1MHz Push-Pull DC/DC Driver with Duty Cycle Control
ADP7118	20V, 200mA, Low Noise, CMOS LDO Linear Regulator
ADP7183	-300 mA, Ultralow Noise, High PSRR, Low Dropout Linear Regulator

Isolated

Multichannel

POWER REQUIREMENTS

PARAMETER	STAGES	Isolation		ADC		Isolated Gate Driver		
	Part #	ADuM252N		AD7606B		ADuM4146		
	Pin	V _{DD1}	V _{DD2}	V _{CC}	V _{DRIVE}	V _{DD1}	V _{DD2}	V _{SS2}
Supply Voltage	V	3.3	3.3	5	3.3	3.3	15	-3
Supply Current	mA	19.4	19.8	47.5	1.5	5.89	4.37	6.21
PSRR	dB	-		68 (100kHz)		-		

Note 1: The supply currents indicated are the maximum quiescent current of the supply rails. For overall full load or short circuit current specifications, refer to the datasheets of the signal chain components.

Note 2: The supply voltages indicated are the values for typical applications.

Note 3: Consult the corresponding datasheets for details on power dissipation if needed.

Note 4: The actual supply current requirement shall be multiplied depending on the number of channels on the signal chain.